

ENGLISH

Datasheet

RS Pro 160mA Radial Non-Resettable Wire Ended Fuse, 250 V RS Stock No: 767-5014

Product Details

RS Pro radial non-resettable fuse withstands currents up to 160 mA and voltages up to 250 V. It has thermoplastic body for added durability. This slow blow fuse forms a convenient and reliable solution to a vast array of application requirements.

Features and Benefits

- Slow blow fuse
- Base and cap in black thermoplastic
- Round pins in tin plated copper
- Vibration MIL-STD-202G
- Salt spray MIL-STD-202G
- Insulation resistance MIL-STD-202G
- Resistance to solder heat MIL-STD-202G
- Thermal shock MIL-STD-202G



ENGLISH

Specifications: Body Height 7.7 mm **Body Length** 8.35 mm **Body Material** Thermoplastic **Body Width** 4.3 mm Breaking Capacity (at Maximum 35 A at 250 V ac Voltage Rating) 160 mA Current Rating Radial Lead Orientation Maximum Operating Temperature +125°C Minimum Operating Temperature -55°C Voltage Rating 250 V 250 V Voltage Rating Wire Diameter 0.62 mm Wire Length 22 mm Wire Pitch 5.08 mm Fuse Type Time Lag Nominal Resistance 1.2458 Ω SEMKO, VDE, TUV, CSA, UL, CCC, Standards Met KTL, RoHS