



Part Number : [38001348](#)

Product Description : KK 254 PC Board Connector, Right-Angle, with Cat Ear Terminal, 18 Circuits

Series Number : 4455

Status : Active

Product Category : PCB Headers and Receptacles

Engineering Number : A-4455-AZ18C(P909)



Documents & Resources

Drawings

[038001348_sd.pdf](#)

[PK-44646-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


Specifications

[PS-10-07-001.pdf](#)

[PS-99020-0088-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|-----------------------------------------------------------------------------------------------------------|
| GADSL/IMDS | Compliant with Exemption 44 |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|----------------|----------------------------------------------------------------------------|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 4455 |
| Description | KK 254 PC Board Connector, Right-Angle, with Cat Ear Terminal, 18 Circuits |
| Application | Board-to-Board, Signal |
| Component Type | PCB Receptacle |
| Product Name | KK 254 |
| UPC | 800753732056 |

Agency

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 2.5A |
| Grounding to PCB | No |
| Voltage - Maximum | 500V |

Physical

| | |
|--------------------------------|---------------------------|
| Circuits (Loaded) | 18 |
| Circuits (maximum) | 18 |
| Color - Resin | Natural (White) |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | None |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 1.941/g |
| Number of Rows | 1 |
| Orientation | Right Angle |
| Packaging Type | Tray |
| PCB Locator | No |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.60mm |
| PC Tail Length | 3.30mm |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Plating min - Mating | 1.016µm |
| Plating min - Termination | 1.016µm |
| Polarized to PCB | Yes |
| Temperature Range - Operating | See Product Specification |
| Termination Interface Style | Through Hole |

Solder Process Data

| | |
|------------------------------|------|
| Max-Duration | 5 |
| Lead-Free Process Capability | WAVE |
| Max-Cycle | 1 |
| Max-Temp | 235 |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|---------------------------------------------------------------|---------------|
| KK 254 RPC Vertical Headers with Friction Lock | <u>171856</u> |
| KK 254 RPC Right-Angle Headers with Friction Lock | <u>171857</u> |
| KK 254 Single Row Vertical Headers | <u>4030</u> |
| KK 254 Single Row Right-Angle Headers | <u>4094</u> |
| KK 254 Vertical Breakaway Headers with Friction Lock | <u>42375</u> |
| KK 254 Right-Angle Breakaway Headers | <u>42376</u> |
| KK 254 Right-Angle Surface Mount Compatible Breakaway Headers | <u>42377</u> |