



PRODUCT-DETAILS

K6S-31Z-1.7-71

K6S-31Z-1.7-71Mini Contactor Relay24 V
DC3NO1NCScrew Terminals



General Information	
Extended Product Type	K6S-31Z-1.7-71
Product ID	GJH1213001R7311
EAN	4013614240300
Catalog Description	K6S-31Z-1.7-71Mini Contactor Relay24 V DC3NO1NCScrew Terminals
Long Description	The K6S-31Z mini contactor relay is a compact 4 pole contactor relay with screw terminals. They are ideally suited for applications where reliability is a must and space is at a premium. Mini contactors relays are used in residential buildings, commercial buildings and industrial applications for switching of control signals up to 3 A / 400 V (AC-15). Due to the low coil consumption, this device can be directly controlled by a PLC. Further features are the noiseless and hum-free coil, the integrated protective circuit with diodes and additional overvoltage protection, a switch position indication and the integrated possibility for rail or wall mounting. The integrated surge suppressor saves time and costs by avoiding the need to install an external suppressor circuit.
Ordering	
Minimum Order Quantity	1 piece
Customs Tariff Number	85365080

Popular Downloads

EPLAN Data	9AAC202720_EPLAN
Data Sheet, Technical Information	1SBC100214C0202
Instructions and Manuals	2CDC102047M6801
CAD Dimensional Drawing	2CDC001079B0201

Dimensions

Product Net Width	52.5 mm
Product Net Depth / Length	46.5 mm
Product Net Height	57.5 mm
Product Net Weight	0.175 kg
Dimension Diagram	GJL1200436F0001

Technical

Number of Main Contacts NO	0
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	3
Number of Auxiliary Contacts NC	1
Number of Poles	4P
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1
Rated Operational Voltage	Auxiliary Circuit 690 V AC Auxiliary Circuit 250 V DC
Rated Frequency (f)	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC Control Circuit DC Main Circuit 60 Hz Main Circuit 50 Hz Main Circuit DC
Conventional Free-air Thermal Current (I_{th})	Auxiliary Circuit 6 A
Rated Operational Current AC-15 (I_e)	(24 V) 4 A (120 V) 4 A (240 V) 4 A (400 V) 3 A (500 V) 2 A
Rated Operational Current DC-13 (I_e)	(24 V) 2.5 A (110 V) 0.7 A (220 / 240 V) 0.4 A
Short-Circuit Protective Devices	gG Type Fuses 6 A
Rated Insulation Voltage (U_i)	690 V acc. to UL/CSA 600 V
Rated Impulse Withstand Voltage (U_{imp})	Auxiliary Circuit 6 kV
Maximum Electrical Switching Frequency	(AC-15) 600 cycles per hour (DC-13) 600 cycles per hour
Mechanical Durability	Nr. Operations 10000000 cycle
Minimum Switching Capacity	17 V 5 mA
Coil Operating Limits	(acc. to IEC 60947-4-1) for DC supply U_c Min. ... U_c Max. (at $\theta \leq 55^\circ\text{C}$) (acc. to IEC 60947-5-1) for DC supply 0.85 ... 1.1 x U_c (at $\theta \leq 55^\circ\text{C}$)
Rated Control Circuit	24 V DC

Voltage (U_e)

Coil Consumption	Average Holding Value 50 Hz 35 V-A Average Pull-in Value 50 Hz 35 V-A
Power Loss	at Rated Operating Conditions per Pole 0.32 W
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm² Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm² Flexible 1/2x 1 ... 2.5 mm² Rigid 1/2x 1 ... 4 mm²
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 1 ... 2.5 mm² Flexible with Insulated Ferrule 1/2x 1 ... 2.5 mm² Flexible 1/2x 1 ... 2.5 mm² Rigid 1/2x 1 ... 4 mm²
Wire Stripping Length	Auxiliary Circuit 9 mm
Degree of Protection	Auxiliary Circuit Terminals IP20 Control Circuit Terminals IP20 Main Circuit Terminals IP20
Recommended Screw Driver	M3 Pozidriv 1
Tightening Torque	Auxiliary Circuit 0.8 ... 1.1 N·m Control Circuit 0.8 ... 1.1 N·m Main Circuit 0.8 ... 1.1 N·m
Terminal Type	Screw Terminals
Mini Contactor Type	Interface Mini Contactor Relay
Product Name	Mini Contactor Relay
Remarks	No CA6 or CAF6 mountable

Technical UL/CSA

Maximum Operating Voltage UL/CSA	600 V AC
General Use Rating UL/CSA	(600 V AC) 5 A
Connecting Capacity Auxiliary Circuit UL/CSA	Stranded 1/2x 22-10 AWG
Contact Rating UL/CSA	A600
Tightening Torque UL/CSA	Auxiliary Circuit 7 in-lb Control Circuit 7 in-lb

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +80 °C
Maximum Operating Altitude Permissible	2000 m
Resistance to Shock acc. to IEC 60068-2-27	11 ms Pulse 15g
Resistance to Vibrations	3g 3 ... 150 Hz

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2021-006202
RoHS Declaration	2CMT2021-006277
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006525
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

ABB EcoSolutions	
End Of Life Disassembling Instructions	1SBC100156C0269
Environmental Product Declaration - EPD	1SAC200409H0001

Certificates and Declarations	
CB Certificate	1SAA938001-2001
Declaration of Conformity - CE	1SAD101100-3101
Declaration of Conformity - UKCA	1SAD201100-3101
EAC Certificate	1SAA938001-2701
RMRS Certificate	1SAA938001-0704

Container Information	
Package Level 1 Units	box 10 piece
Package Level 1 Width	115 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Height	54 mm
Package Level 1 Gross Weight	1.82 kg
Package Level 1 EAN	4013614411212

External Classifications and Standards	
Object Classification Code	K
ETIM 7	EC000196 - Contactor relay
ETIM 8	EC000196 - Contactor relay
ETIM 9	EC000196 - Contactor relay
eClass	V11.0 : 27371001
UNSPSC	39121529
IDEA Granular Category Code (IGCC)	4763 >> Power contactor, DC switching

Categories	
Low Voltage Products and Systems → Control Products → Contactors → Mini Contactor Relays	

