

PENKO Engineering B.V. When Weighing Counts

FLEX2100 specs extended



| SPECIFICATIONS FLEX2100 Range | |
|--------------------------------------|---|
| Wiring | Full Wheatstone bridge with passive connections (6-wire system) |
| Sense system | Passive sense system |
| Excitation voltage | 5VDC |
| Minimum bridge resistance | 43.75Ω @ 5V excitation |
| Maximum bridge resistance | 1200Ω @ 5V excitation |
| Number of load cells | 1 channel 1 - 8 load cells 350Ω @ 5V excitation 1 - 22 load cells 1000Ω @ 5V excitation |
| Sensitivity | Certified: 0.4μV minimum voltage for verification scale @ 5V excitation Non-certified: 0.1μV - 0.5μV @ 5V excitation |
| Selectable ranges | 1, 1.5, 2, 2.5, 3mV/V |
| Input voltage unipolar @3mV/V | -1mV to 16mV |
| Input voltage bipolar @3mV/V | -16mV to 16mV |
| A/D conversion speed | 1600 measurements per second |
| Internal resolution | 24 bits |
| A/D converter type | Sigma-Delta, ratio metric, isolated from digital |
| Non linearity | < 0.005% of reading |
| Offset drift | < +/- 2 ppm/°C |
| Span drift | < +/- 2 ppm/°C |
| Display resolution | 100,000 divisions max. (certified with 10,000 divisions) |
| Display step | x1, x2, x5, x10, x20, x50, x100, x200 |
| Decimal comma | Selectable between any digits of the display value |
| Digital filter | High performance digital filters 1-10Hz |
| Overall filter | 0 to -48dB |
| Calibration methods | Dead load and span with up to 8 point linearization Millivolt calibration G - CAL (Gravity correction) |

PENKO Engineering B.V. When Weighing Counts

FLEX2100 specs extended

| | |
|-------------------------|--|
| Measurement functions | Automatic zero tracking, motion detection, zero, tare, preset tare, net mode, peak hold, valley hold, bar graphs, multi range, multi interval |
| Memory allocation | Calibration data flash, dynamic data in SRAM with battery backup |
| Real-time clock | Standard with rechargeable Lithium battery backup |
| SCREEN | |
| Display type | High resolution TFT LCD 640 x 480 pixels, 256 colors, high brightness 500cd/m ² , high contrast 350:1 |
| Display functions | Completely menu driven with graphical user interface |
| Display rate | Selectable 1, 2, 3, 5, 10 or 25 updates/s |
| Display filter | 0, -6, -12, -18, -24, -30, -36, -42, -48dB |
| Display filter range | Selectable in any range of the display value |
| Display suppression | Selectable in any range of the display value |
| Status enunciators | Zero, Net, No motion, Bar graph, I/O status |
| Display digits | 6 digits with leading zero suppression, selectable height; 9 or 18mm |
| Display operation | Operate, configure and calibrate via: <ul style="list-style-type: none"> - Front panel (touch screen) - RS232 - Ethernet - USB |
| Touch screen | Glass screen, 2mm of resistive type |
| Display size | 5.7 inch (145mm) |
| Display material | Front foil PET 175 μ |
| ENVIRONMENTAL | |
| Operating temperature | -10°C to +40°C [14°F to 104°F] |
| Storage temperature | -20°C to +70°C [-4°F to 158°F] |
| Relative humidity | Max. 85% non-condensing |
| APPROVALS | |
| Non automatic OIML R76 | 10,000d single or multi interval at $\geq 0,4\mu\text{V}$ scale interval |
| EU-type approval number | T 2804 |
| Automatic MID certified | |
| OIML R50 | Continuous totalizer beltweiger |
| OIML R51 | Automatic catchweigher/checkweigher instrument |
| OIML R61 | Automatic gravimetric filling instrument |
| OIML R107 | Discontinuous totalizer |

PENKO Engineering B.V. When Weighing Counts

FLEX2100 specs extended

| | |
|-------------------------------------|--|
| EU-test/evaluation certificate | TC7927 |
| EU-type approval numbers | |
| OIML R107 | T 10301 |
| OIML R51 | T 10303 |
| OIML R61 | T 10304 |
| ENCLOSURE PANEL MOUNT | |
| Material | Housing: extruded aluminum, black powder coating Front: machined aluminum, black anodized |
| Dimensions front (w*h*d) | 260 x 191 x 5mm |
| Dimensions housing (w*h*d) | 220 x 150 x 48mm |
| - panel cut out (w*h) | 224 x 154mm |
| Weight without option boards | 1700g |
| Mounting clips | 2 mounting clips |
| Rubber seal | O-ring of mosrubber |
| Protection class | IP45 (or IP65 when built into a cabinet) |
| ENCLOSURE STAINLESS STEEL | |
| Material | Stainless steel |
| Dimensions front (w*h*d) | 240 x 180 x 70mm |
| Dimensions housing (w*h*d) | 280 x 200 x 70mm |
| Weight | 2300g |
| Protection class | IP65 |
| ELECTRICAL OPTIONS | |
| AC power supply | 100 - 240VAC 50/60Hz 20W max. |
| DC power supply | 18 - 32VDC (24VDC type) 20W max. |
| STANDARD COMMUNICATION PORTS | |
| RS232 /RS422 | Plain text/ASCII printer, Zebra ZPL protocol, PENKO ASCII, PENKO NPV slave and master, PENKO TP slave and master, Modbus RTU and ASCII, Hostlink Viewteq and PLC |
| Ethernet | PENKO TP protocol, plain text/ASCII printer, Zebra ZPL protocol, Modbus TCP, EtherNet/IP, Omron Fins, PENKO Buslink, PENKO Web interface |
| USB | Reporter, PENKO ASCII, TP slave Host functionality for USB storage (FAT16) or HID class keyboard or mouse |
| CANBUS | PENKO Buslink |




PENKO Engineering B.V. When Weighing Counts

FLEX2100 specs extended

| OPTIONAL COMMUNICATION PORTS | |
|-------------------------------------|---|
| PROFIBUS | DP Slave |
| | |
| COMMUNICATION SOFTWARE | |
| Pi Mach II | PENKO configuration, update and backup/restore software (free) |
| PDI Client | PENKO configuration software (free) |
| Profibus | GSD file |
| EtherNet/IP | EDS file |
| | |
| STANDARD DI & DO | |
| 8 digital inputs | Optical isolated, 1 common, 18-28VDC, PNP or NPN Input 1 can be used as: a normal input or as a counter input (<= 5kHz @ 24VDC with 50% duty cycle) Before 2018: counter input <= 1kHz, on request 5kHz. Since 2018: counter input <= 5kHz @24Vdc with 50% duty cycle. |
| 8 digital outputs (level contact) | Isolated PhotoMOS outputs, 2 common, max. 35VDC or VAC, 0.5A nominal, 1A Surge (thermal fuse 0.5A), PNP or NPN |
| | |
| OPTIONAL I/O | |
| 1 analog output | 0 - 20mA, 4 - 20mA, 0 - 24mA, 4 - 24mA, RAW |
| | |

PENKO Engineering B.V. When Weighing Counts


FLEX2100 specs extended



| Panel mount housing | |
|-------------------------------|---|
| Material housing | Extruded aluminum, black powder coating |
| Front machined aluminum | Black anodized |
| Dimensions front: W x H x D | 260 x 191 x 5 mm |
| Dimensions housing: W x H x D | 220 x 150 x 48 mm |
| Dimensions panel cut out | 224 x 154 mm |
| Weight approx. | 1700 g. |
| Mounting clips | 2 mounting clips |
| Rubber seal | O-ring of mosrubber |
| Build in chipset | IP 45 |

If build in a cabinet (Front)

IP 65



PENKO Engineering B.V. When Weighing Counts

FLEX2100 specs extended



Stainless steel mount housing

| | |
|-------------------------------|--|
| Material housing | Stainless steel |
| Dimensions front: W x H x D | 240 x 180 x 70 mm |
| Dimensions housing: W x H x D | 280 x 200 x 70 mm (including nuts and bracket) |
| Weight approx. | 2300 g. |
| Protection | IP 65 |



About PENKO

At PENKO Engineering we specialize in weighing. Weighing is inherently chemically correct, independent of consistency, type or temperature of the raw material. This means that weighing any kind of material guarantees consistency and thus, it is essential to sustainable revenue generation in any industry. As a well-established and proven solution provider, we strive for the ultimate satisfaction of custom design and/or standard applications, increasing your efficiencies and saving you time, saving you money.

Whether we are weighing raw materials, components in batching, ingredients for mixing or dosing processes, - or weighing of static containers and silos, or - in-motion weighing of railway wagons or trucks, by whatever means required during a process, we are essentially forming vital linkages between processes and businesses, anywhere at any time. We design, develop and manufacture state of the art technologically advanced systems in accordance with your strategy and vision. From the initial design brief, we take a fresh approach and a holistic view of every project, managing, supporting and/or implementing your system every step of the way. Curious to know how we do it? www.penko.com

Certifications

PENKO sets high standards for its products and product performance which are tested, certified and approved by independent expert and government organizations to ensure they meet – and even – exceed metrology industry guidelines. A library of testing certificates is available for reference on:

http://penko.com/nl/publications_certificates.html

PENKO Professional Services

PENKO is committed to ensuring every system is installed, tested, programmed, commissioned and operational to client specifications. Our engineers, at our weighing center in Ede, Netherlands, as well as our distributors around the world, strive to solve most weighing-system issues within the same day. On a monthly basis PENKO offers free training classes to anyone interested in exploring modern, high-speed weighing instruments and solutions. Training sessions on request: www.penko.com/training



PENKO Alliances

PENKO's worldwide network: Australia, Brazil, China, Denmark, Germany, Egypt, Finland, France, India, Italy, Netherlands, Norway, Poland, Portugal, Slovakia, Spain, Syria, Turkey, United Kingdom, South Africa, Slovakia Sweden and Switzerland, Singapore.

A complete overview you will find on: www.penko.com/dealers

