


Features

- UL94HB flame rated Nylon 66 with metal powder.
- Color: Blue, other special color available request.
- Releasable and reusable.
- Excellent chemical resistance.

RS PRO Metal Detectable Releasable Cable Ties

RS Stock No.: 1721769



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Metal Content Tie is a cable tie specifically designed for use in the food and pharmaceutical processing industries.
During the manufacturing process, a metallic pigment is included which enables the ties to be detected more readily than standard ties
Metal content cable ties are ideal for fastening cables and hoses in processing and packaging areas to prevent contamination.

General Specifications

Type	Metal Detectable & Releasable
Colour	Blue
Material	PA66MP
Resistant to	Chemical resistance
Quantity	250

Mechanical Specifications

Length	250mm / 10"
Width	4.5mm / 0.18"
Min. Loop Tensile Strength(lbs/kgf/N)	34lbs / 15kgf / 150N
Maximum Bundle Dia.	65mm

Approvals

Standards Met	RoHS, HF
---------------	----------

