



APC Back-UPS Pro, 1200VA/ 720W, Tower, 230V, 6x CEE 7/7 Schuko outlets, AVR, LCD, User Replaceable Battery

BR1200G-GR

Overview

Lead time Usually in Stock

Main

mam	
Main Input Voltage	230 V
Main Output Voltage	230 V
Rated power in W	720 W
rated power in VA	1200 VA
Product or component type	Uninterruptible power supply (UPS)
output connection type	3 Schuko CEE 7 3 Schuko CEE 7 surge
Cable length	1.5 m
Range of product	Back-UPS Pro

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	8 h
Number of battery replacement quantity	2
Battery voltage	24 V
Battery capacity	9.0 Ah
Battery charger power	23 W rated
Extended runtime	0
Replacement battery	APCRBC124 ☐

General

Provided equipment	telephone cable user manual USB cable warranty card
Number of power module free slots	0
Number of power module filled slots	0

Rates duty January 2016

Redundant	No

Physical

Height	30.1 cm
Width	11.2 cm
Depth	38.2 cm
Net weight	13 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

Input

•	
Network frequency	50 Hz +/- 1 Hz 60 Hz +/- 1 Hz
Input voltage limits	156300 V adjustable 176294 V
Maximum input current	10 A
Switching current capacity	10 A

Output

<u> </u>	
Maximum configurable power in W	720 W
Output frequency	50/60 Hz +/- 1 Hz sync to mains 50/60 Hz +/- 1 Hz unsynchronised
UPS type	Line interactive
Wave type	Stepped approximation to a sinewave
Bypass type	Built-in bypass
Maximum configurable power in VA	1200 VA
Transfer time	10 ms typical : 12 ms maximum

Conformance

Product certifications	BSI 1363 CE NEMKO
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Equipment protection policy	Lifetime : 200000 AUD Lifetime : 150000 euros Lifetime : 75000 GBP

Environmental

Ambient air temperature for operation	040 °C
Relative humidity	095 %
Operating altitude	010000 ft
Ambient air temperature for storage	-1545 °C

Storage Relative Humidity	095 %
Storage altitude	0.000000000015240.000000000 m
Acoustic level	45 dBA

Surge Protection and Filtering

Surge energy rate	441 J
Data line protection	RJ11 modem/fax/DSL protection (two wire single line)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.000 cm
Package 1 Width	39.000 cm
Package 1 Length	49.000 cm
Package 1 Weight	13.000 kg
Unit Type of Package 2	P12
Number of Units in Package 2	12
Package 2 Height	90.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	168.000 kg
SCC14	10731304286834

Contractual warranty

Warranty

2 years repair or replace, 3 years repair or replace for European Union countries



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	019b51cf-d7f1-4f06-ac85-1378fc94c7aa
REACh Regulation	REACh Declaration
♥ Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

BR1200G-GR

Image of product / Alternate images

Alternative

