

## Sterile polyisoprene gloves, designed for Class 100 (ISO 5)/Grade A cleanroom environments

- **Elevated comfort:** Ideal for double gloving, TouchNTuff® 83-500 polyisoprene cleanroom gloves' ultra-soft polyisoprene offers "second skin"-like comfort and minimizes hand fatigue with prolonged wear
- **Reduced allergy risks:** They contain no latex proteins, meaning they do not pose any threat related to Type I latex allergies and sensitivities
- **Sterility assurance:** These disposable gloves are sterilized by gamma irradiation, with a sterility assurance level (SAL) of 10<sup>-6</sup>



### KEY FEATURES & BENEFITS

- **Ultra-soft polyisoprene:** "Second skin" comfort and feel
- **Latex-free design:** Latex Type I allergy risks eliminated
- **Gamma sterilization:** A sterility assurance level (SAL) of 10<sup>-6</sup>

### Industries

- Laboratory Maintenance & Clean-Up
- Pharmaceutical Manufacturing
- Biotechnology Manufacturing
- Medical Device Manufacturing
- Laboratory Research and Development
- Preparation of Materials
- Production & Processing
- Lab and R&D
- Controlled and Critical Environments
- Production and Manufacturing

### Recommended For

- Maintaining lab furniture and equipment
- Spill or leakage cleanup
- Transferring liquids and solids
- Packaging and labeling
- Clean room cleaning and preparing
- Sample taking and processing
- Administering drugs
- Transferring liquids and solids between vessels and tanks and process equipment



## TECHNICAL DATA SHEET

	Product Information
Material	PI (Polyisoprene)
Color	White
Shape	Anatomic with Curved Fingers
Cuff	Beaded with SUREFIT™ Technology
Manufacturing/QMS Audit Standards	ISO 13485, ISO 9001:2015, Manufacturing QMS Audit Standards ISO 9001, PPE Regulation 2016 425 Module D
Regulatory/Standard Compliance	AS/NZS 4179, ASTM D3577, ASTM D7160, CE 0493, EN 556-1:2001, EN ISO 21420:2020, EN ISO 374-1:2016 Type B (KPT), EN ISO 374-5:2016, EN 421:2010, Please consult the IFU, ISO 10282, ISO 11193, Category III, UKCA
Packaging	<p>1 pair per inner polybag; 10 pairs per outer polybag; 5 polybags per master polybags; 4 master polybags per carton; 200 pairs per carton</p> <p><b>More sustainable packaging:</b> These sterile gloves are packed in recyclable plastic packaging* and delivered in recycled cardboard shipper cases.</p> <p>*Inner wrap, pouch, bag and liner are made from polyethylene (PE) based film. Always check your local recyclable status as these materials may not be considered suitable for recycling in your location.</p>
Storage	Keep away from direct sunlight; store in a dry place and keep in the original packaging. Keep away from ozone sources. If products are properly stored, as indicated, they won't lose their performances or change characteristics significantly. If products could be affected by ageing or storage, the expiry date is mentioned on the packaging materials.
Country of Origin	Sri Lanka
Available sizes	5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9
Powder Content	Powder-Free
External Glove Surface	Smooth
Internal Glove Surface	Polymer Coated with DERMASHIELD™ Technology
Sterilization Method	GAMMA irradiation (25 kGy)
Cleanroom Class	Class 100/ISO Class 5 & EU GMP Grade A/B and other sterile cleanrooms
Shelf Life	5 Years
Tested for use with Chemotherapy Drugs	Yes
Protein Level	N/A: contains no natural rubber latex
Anti-static	No
Vulcanization Chemical Accelerators	<ul style="list-style-type: none"> <li>• Xanthates</li> <li>• Zinc Dialkyldithiocarbamate</li> </ul> <p><i>Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.</i></p>

Physical Properties		Testing Method
Typical Length (mm/in)	300 / 12	EN 420/ASTM D3767
Freedom from Holes	0.65 AQL	EN 455-1/ASTM D3577
Typical Particle Count $\geq 0.5\mu\text{m}$ (counts / $\text{cm}^2$ )	$\leq 2500$	IENT-RP-CC005.4
Target Single Wall Palm Thickness (mm/mil)	0.21 / 8.26	EN 420/ASTM D3767
Target Single Wall Finger Thickness (mm/mil)	0.23 / 9.05	EN 420/ASTM D3767
Target Single Wall Cuff Thickness (mm/mil)	0.17 / 6.69	EN 420/ASTM D3767
Ultimate tensile strength (MPa) Before Aging	$\geq 17$	ASTM D412-06a
Ultimate tensile strength (MPa) During Aging	$\geq 12$	ASTM D412-06a
Force at Break (N) Before Aging	9	EN 455-2
Force at Break (N) During Aging	9	EN 455-2

## ORDERING INFORMATION

SIZE	5.5	6	6.5	7	7.5	8	8.5	9
REORDER NO.	83500055	83500060	83500065	83500070	83500075	83500080	83500085	83500090

## PERFORMANCE STANDARDS AND REGULATORY COMPLIANCE



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
US T: +1 800 800 0444  
US F: +1 800 800 0445  
CA T: +1-800-363-8340

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### UK

Ansell Nitritex  
T: +44 1638 663338  
F: +44 1638 668890

## Technology



Pinhole Barrier Technology



Ergonomic Design Technology



Cuff Roll-down Technology



Donning Aid Technology



Skin-friendly, non-sensitizing  
PI Technology