

Product data sheet

Characteristics

C16L4

circuit breaker basic frame, ComPacT

NSX160L, 150 kA at 415 VAC 50/60 Hz, 160 A, without trip unit, 4 poles



Main

Range	ComPacT new generation
Product name	ComPacT NSX new generation
Device short name	NSX160L
Product or component type	Basic frame
Device application	Distribution
Poles description	4P
Neutral position	Left
[In] rated current	160 A at 40 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category A
[Icu] rated ultimate short-circuit breaking capacity	130 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 KA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 KA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 20 KA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 50 KA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 70 KA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	L 150 kA 415 V AC
Control type	Toggle
Mounting mode	Fixed

Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	130 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 KA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 KA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 20 KA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 50 KA at 525 V AC 50/60 Hz conforming to IEC 60947-2 70 KA at 500 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical durability	40000 cycles conforming to IEC 60947-2
Electrical durability	40000 Cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2 15000 Cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 20000 Cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 7500 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
Connection pitch	35 mm
Protection type	Without protection
Width (W)	140 mm

Height (H)	161 mm
Depth (D)	86 mm

Environment

Standards	EN/IEC 60947-2 UL 508
Product certifications	CSA UL
Pollution degree	3 conforming to IEC 60664-1
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 62262
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	14.5 cm
Package 1 Length	19.0 cm
Package 1 Weight	1.956 kg
Unit Type of Package 2	S03
Number of Units in Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.118 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------