

CUT PROTECTION

COLD PROTECTION

Tromso+

Thin and flexible fully coated insulated glove with high cut protection

Lightweight, fleece-lined cut resistant glove with a breathable microporous nitrile coating providing excellent grip in dry and wet conditions.

Features

- ▲ Fully dipped nitrile foam allowing good grip in wet and dry conditions
- ▲ Soft fleece lining for comfort in cold conditions
- ▲ Durable and lightweight coating ensures glove longevity in abrasive applications
- ▲ Touchscreen capabilities to allow usage with screen devices
- ▲ Sanitised antimicrobial finish provides extra freshness
- ▲ Contact heat protection up to 250°C / 482°F for a short period (15 sec max)



Certifications



Suitable industries & applications

Industries

- ▲ Construction
- ▲ Highways and Infrastructure
- ▲ Utilities
- ▲ Waste and Recycling

Applications

- ▲ Civil Engineering
- ▲ Glass and Glazing
- ▲ Highway Repairs and Maintenance
- ▲ Labouring
- ▲ Public Works
- ▲ Working in Extreme Temperatures

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.



CUT PROTECTION

COLD PROTECTION

Tromso+

Thin and flexible fully coated insulated glove with high cut protection

Product information

Materials	Liner:	13 Gauge Engineered HPPE, Steel Fibre, Nylon, Acrylic, HPPE
	Coating:	Microporous Nitrile
Colour	Black / Orange	
Length	230mm	
Cuff Style	Elasticated Knit Wrist	

Ordering information

S	SKG00097FD	Items per Pack 10 x Pairs
M	SKG00097FF	
L	SKG00097FH	Items per Case 60 x Pairs
XL	SKG00097FJ	
XXL	SKG00097FL	

Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.

 **GLOBUS**