



PLT12EH-Q0




- Greater resistance to damage caused by ultraviolet light – indoor or outdoor use
- Typically used for heavy duty applications such as securing conduit or large cable bundles to permanent structures
- Strongest *Pan-Ty*® Cable Tie available
- Can be used with mounting clip (MCEH-S25-C0)

■ Part Number	PLT12EH-Q0
■ RoHS Compliancy Status	Compliant
■ Part Description	Cable Tie, 40.1", Extra-Heavy cross section
■ Product Type	Cable Ties
■ Material	Weather Resistant Nylon 6.6
■ Color	Black
■ CSA Certified	No
■ UL Listed (File #E56854)	No
■ UL Recognized (File #E56854)	No
■ Length (In.)	40.1
■ Length (mm)	1019
■ Width (In.)	.500
■ Width (mm)	12.7
■ CE Compliant	Yes
■ Cross Section	Extra-Heavy
■ Head Height (In.)	.400
■ Head Height (mm)	10.2
■ Head Width (In.)	.800
■ Head Width (mm)	20.3
■ Locking Style	Locking
■ Material Flammability Rating	UL 94-HB
■ Max. Bundle Diameter (In.)	12.00
■ Max. Bundle Diameter (mm)	305
■ Max. Continuous Use Temperature	185°F (85°C)
■ Min. Loop Tensile Strength (Lbs.)	250
■ Min. Loop Tensile Strength (N)	1112

■ Pricing Description	Cable Tie, 40.1"L (1019mm), Extra-Heavy, Weather Resistant, Black
■ Thickness (In.)	.085
■ Thickness (mm)	2.2
■ Tool	GS4EH, ST3EH
■ Min. Order UOM	PC
■ Min. Order Qty.	25
■ BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PLT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PLT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PLT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PLT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2223)
PLT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PLT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	CAD FILENAME/LAYERS	DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.	
										<p>PANDUIT CORP. TINLEY PARK, ILLINOIS</p> <p>PAN-TY® NON-RELEASABLE LASHING TIES</p> <p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1(2.5) (.XXX) ± .010(.25) (.XX) ± .02(.5) ANGLES ± -----</p> <p>UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.</p>	
									DRAWN BY L. VALDES	MAT'L: NYLON 6/6	SCALE NONE
8	4/27/04	JABO		CORRECTED METRIC CONVERSION OF PLT5EH AND PLT12EH, F DIM	6512	8			DATE 7-15-77		DRAWING NO. SS-6512
									CHK'D HVP		DWG A SIZE