



CIRCUIT	0	C30	120°
1-2			
1-3			
			120°/300°
4-6			
4-5			
	0°	30°	330°



CHARACTERISTICS

ELECTRICAL CHARACTERISTICS

standard switch : CEE 24
 Rated amperage : 16(4) A
 Rated voltage : 250 V
 Type of current : Vac
 Switch configuration : DPDT
 Switch for appliance classe II
 Number of electrical operations : 10 000
 connections terminal : 6.35 x 0.8

MECHANICAL CHARACTERISTICS

Winding torque : 1.5 to 4.5 Kg.cm
 Return torque to zero position : 1 to 4.5 Kg.cm
 timing : 120 min
 timing range : ±5%
 Residual operating torque : 0.1 Kg.cm
 Torque of manual position : /

THERMAL CHARACTERISTICS

Maximum temperature of use : 125° C

MARKING ON BACK CASE

Type MI2
 T= 125°C
 Identification of terminals

APPROVALS

UL- SEMKO- ENEC10 VDE- CSA- IMQ
 16A 250V AC RESISTIVE
 4A 250V AC INDUCTIVE

MARKING

Label of the timer : 4 numbers
 week of production : 2 numbers
 Year of production : 2 numbers

CUSTOMER	WEIGHT BY 1000	USE: C53
CUSTOMER PART NUMBER : 1625-561222362	COLOR: BLACK	SETS MI2
MI2/120/300/330/14400L/C30/AM000/23/22.5/6MT4.6		2096 D
DRAWN BY : MARTINET.C	DATE: 19/01/06	SCALE: 1/1