

SES® strain relief bushes DM
in Polyamide 6 black and white
for torsional protection




DM-SES®




DM-SES


Material: polyamide 6
Colours: black - white
Operating temperature: -20 to +70°C
Tensile strength at break: 80 MPa
Ultimate elongation: > 50%
Dielectric strength: 60 kV/mm
Flame resistance: V2 UL94 (internal test)
Application: for passing a cable through a wall with cable clamp.




type	art. no.		dimensions of the cables (mm)		dimensions (mm)					
	black 010	white 001	Ø PVC insulation	Ø rubber insulation	Ø A	B	bore a b		Ø C	
round cables										
DM 2	0131 0012 010	0131 0012 001	3 ... 4,5	3 ... 4,5	9,5	8,5	1,7	10,3	11	100
DM 2L	0131 0032 010	0131 0032 001	3 ... 4,5	3 ... 4,5	9,5	8,5	3,1	10,3	11	100
DM 4	0131 0001 010	0131 0001 001	5 ... 6,5	5 ... 7	13	11,5	2,5	12	14	100
DM 5	0131 0010 010	0131 0010 001	6,5 ... 7,5	6,5 ... 7,5	13	11,5	2,5	11	14	100
DM 6	0131 0002 010	0131 0002 001	6,6 ... 8	7,1 ... 9	16	14	3,5	17	18	100
DM 7	0131 0003 010	0131 0003 001	8,1 ... 10	9,1 ... 11	22,5	21	3,2	20	25	100
DM 8	0131 0004 010	0131 0004 001	10,1 ... 12,5	11,1 ... 14	22,5	21	3,6	22	22	100
flat cables										
			H x W	H x W	Ø A	B	a	b	Ø C	
DM 2P	0131 0022 010	0131 0022 001	3 x 5	3 x 5	9,5	8,5	1,7	10,3	11	100
DM 2LP	0131 0042 010	0131 0042 001	3 x 5	3 x 5	9,5	8,5	3,1	10,3	11	100
DM 4P	0131 0020 010	0131 0020 001	3 x 7,6	3,8 x 7,1	13	11,5	2,8	10,5	14	100
DM 6P	0131 0021 010	0131 0021 001	5 x 9	5 x 9	16	14	3	17	18	100



Round bore (ØA)
 For torsional protection of strain relief grommets, an oblong bore (B) is required.



principle of cable clamping



• DM application tool

Rack and pinion pliers with adjustable jaws to apply all types of strain relief grommets DM-SES for small or mid-sized series.

type	article number	characteristics		
		length (mm)	weight (g)	
R 29	0655 0001 000	180	270	1

