



SENTRON PAC4200; LCD; 96X96MM POWER MONITORING DEVICE PANEL MOUNT TYPE FOR MEASUREMENT OF ELECTR. VALUES VAUX: 110-340VDC / 95-240VAC VIN: MAX.690/400V; 45-65HZ AMPIN: X/1A OR X/5A AC RING LUG TERMINALS

Model		
product brand name		SENTRON
Product designation		multimeter
Design of the product		compact
Product type designation		PAC4200
Type of measured value detection		complete
Design of the power supply		Wide-range power supply
General technical data		
Cutout width	mm	92
Cutout height	mm	92
Size of Power Monitoring Device / company-specific		size 96
Operating mode for measured value detection		
• automatic line frequency detection		Yes
• set at 50 Hz		No
• set to 60 Hz		No
Pulse duration		
• initial value	ms	30
• Full-scale value	ms	500

Voltage curve		Sinusoidal or distorted
Measurable line frequency / initial value	Hz	45
Measurable line frequency / Full-scale value	Hz	65
Measuring procedure / for voltage measurement		TRMS
MTBF	y	169.7
Equipment marking / acc. to DIN 40719 extended according to IEC 204-2 / acc. to IEC 750		P

Voltage

Measurable current / 1 / at AC / Rated value	A	1
Measuring procedure / for current measurement		TRMS

Supply voltage

Supply voltage frequency / Rated value		
• minimum	Hz	45
• maximum	Hz	65
Type of voltage / of the supply voltage		AC/DC
Measuring category / for supply voltage		CATIII
Apparent power consumption		
• with expansion module / maximum	V·A	32
• without expansion module / typical	V·A	11
Active power consumption		
• with expansion module / typical	W	11
• without expansion module / typical	W	5.5
Relative symmetrical tolerance / of the supply voltage	%	10

Protection class

Protection class IP		
• on the front		IP65
Operating resource protection class / when installed		II

Electricity

Short-time current resistance (I_{cw}) / limited to 1 s / Rated value	A	100
Measurable current / 2 / at AC / Rated value	A	5

Suitability

Suitability for operation		Installation in stationary control panels in closed rooms
Adjustable time period / minimum	ms	10

Product function

Product function		
• Illuminance of display backlighting adjustable		Yes
• Time-controlled reduction of the illuminance of display backlighting possible		Yes
• reactive power measurement		Yes

- frequency measurement
- pulse measurement
- Display contrast adjustable
- voltage measurement
- Current measurement
- active power measurement

Yes
Yes
Yes
Yes
Yes
Yes

Display and operation

Design of the display		LCD, graphical, monochrome
Number of keys		4
Color / of the background of the display		white
National language / on the display screen / is supported		ger, en, fr, spa, ita, por, tur, rus, chi, pol
Product function / Display can be inverted (positive <=> negative mode)		Yes
Horizontal image resolution		128
Vertical screen resolution		96

Communication

Refresh time / at the interface		
<ul style="list-style-type: none"> • for instantaneous values / typical 	ms	200
Number of active connections / at the Ethernet interface		3
Number of logical ports / at the Ethernet interface / is supported		2
Design of cable / connectable / Twisted pair		Yes
Product function / at the Ethernet interface		
<ul style="list-style-type: none"> • auto-MDI(X) • Autonegotiation • serial gateway 		Yes Yes Yes
Protocol		
<ul style="list-style-type: none"> • at the Ethernet interface / is supported • is supported 		MODBUS TCP MODBUS TCP
Transfer rate		
<ul style="list-style-type: none"> • minimum • maximum • 1 / for Ethernet • 2 / for Ethernet 	kbit/s kbit/s Mbit/s Mbit/s	10 000 100 000 10 100

Fault limits

Reference condition / for metering accuracy		Acc. to IEC61557-12
Formula for relative total measurement inaccuracy		
<ul style="list-style-type: none"> • for measured variable reactive energy • for measured variable output 		Class 2 according to IEC61557-12 and/or IEC62053-23 +/- 0,5 %

- for measured variable output factor
- for measured variable voltage
- for measured variable current
- for measured variable THD
- for measured variable active energy

+/- 2 %
 +/- 0,2 %
 +/- 0,2 %
 +/- 2 %
 Class 0.2 according to IEC61557-12 and/or class 0.2S according to IEC62053-22

Inputs Outputs

Input voltage / at digital input		
• initial value for signal<1>-recognition	V	19
• at DC / Rated value	V	24
• at DC / maximum	V	30
• Full-scale value for signal<0> recognition	V	10
Number of digital outputs		2
Number of digital inputs		2
Digital output version		switching or pulse output function
Type of switching output		solid state
Type of electrical connection / at the digital outputs		screw-type terminals
Type of electrical connection / at the digital inputs		screw-type terminals
Input current / at digital input		
• for signal <1>	mA	4
Output current		
• at digital output / with signal <0> / maximum	mA	0.2
• at digital output / for signal <1> / maximum	mA	27
• at digital output / for signal <1> / minimum	mA	10
• at the digital outputs / at DC / limited to 100 ms / maximum	mA	300
• at the digital outputs / at DC / maximum	mA	100
Output delay / at digital output		
• for signal <0> to <1> / maximum	ms	5
• for signal <1> to <0> / maximum	ms	5
Operating conditions for digital inputs / external voltage supply		Yes
Operating voltage / as output voltage / at DC / maximum permissible	V	30
Property of the output / Short-circuit proof		Yes
Input delay time / at digital input		
• for signal <0> to <1> / maximum	ms	5
• for signal <1> to <0> / maximum	ms	5
Internal resistance / at the digital outputs	Ω	55
Measuring category / for digital signals		CATI
Switching frequency / at digital output / maximum	Hz	20
Transfer rate / 1 / for fast Ethernet	Mbit/s	100

Measuring inputs

Outer conductors and neutral conductors internal resistance / for voltage measurement	MΩ	1.05
Measurable supply voltage		
• between (PE)N and L / at AC / minimum	V	11.5
• between (PE)N and L / at AC / maximum	V	480
• between (PE)N and L / at AC / maximum rated value	V	400
• between the outer conductors / at AC / minimum	V	20
• between the outer conductors / at AC / maximum	V	828
• between the outer conductors / at AC / maximum rated value	V	690
Voltage measuring range extension / with external voltage transformers		Yes
Measuring category / for voltage measurement		CATIII
Supply voltage / between the outer conductors / at AC / maximum permissible	V	831
Continuous current / at AC / maximum permissible	A	10
Current measuring range extension / with external current transformers		Yes
Measuring category / for current measurement		CATIII
Zero-point suppression / for current measurement		0 ... 10 %
Relative measurable current / at AC		
• minimum	%	1
• maximum	%	120
Apparent power consumption / for current measurement		
• with measuring range 1 A / per phase	mVA	4
• with measuring range 5 A / per phase	mVA	115

Connections

<ul style="list-style-type: none"> • Type of connectable conductor cross-section / at the digital inputs <ul style="list-style-type: none"> — for AWG conductors / solid — solid — finely stranded / with core end processing • Type of connectable conductor cross-section / at the digital outputs <ul style="list-style-type: none"> — for AWG conductors / solid — solid — finely stranded / with core end processing 		<p>1x 24 ... 12</p> <p>1x (0.2 ... 2.5 mm²), 2x (0.2 ... 1.0 mm²)</p> <p>1x (0.25 ... 2.5 mm²), 2x (0.25 ... 1.0 mm²)</p> <p>1x 24 ... 12</p> <p>1x (0.2 ... 2.5 mm²), 2x (0.2 ... 1.0 mm²)</p> <p>1x (0.25 ... 2.5 mm²), 2x (0.25 ... 1.0 mm²)</p>
Type of electrical connection		

- of the fast Ethernet interface

RJ45 (8P8C)

Mechanical Design

Height	mm	96
Height / of the display	mm	54
Width	mm	96
Width		
• of the display	mm	72
Depth	mm	82
mounting position		vertical
Installation depth	mm	77
Installation depth / with expansion module / maximum	mm	99
Mounting type / panel mounting		Yes
Material thickness / of the control panel		
• maximum	mm	4

Environmental conditions

Degree of pollution		2
Installation altitude / at height above sea level / maximum	m	2 000
Standard		
• for EMC for industrial sector		IEC 61000-6-2
• for EMC against unloading		IEC 61000-4-2
• for EMC against high frequency fields		IEC 61000-4-3
• for EMC against conducted LF disturbance variables (industry)		IEC 61000-6-4
• for EMC against conducted disturbance variables via HF fields		IEC 61000-4-6
• for EMC against magnetic fields with power engineering frequencies		IEC 61000-4-8
• for EMC against quick, transient electrical disturbances		IEC 61000-4-4
• for EMC against voltage drops and interruptions		IEC 61000-4-11
• for EMC against surge voltages		IEC 61000-4-5
• for free fall		IEC 60068-2-32
• for pulse emitter		according to IEC62053-31
• for cyclic, environmental damp heat check		IEC 60068-2-30
• for environmental coldness check		IEC 60068-2-1
• for environmental dry heat check		IEC 60068-2-2
Relative humidity / at 25 °C / without condensation / during operation		
• minimum	%	5
• maximum	%	95

Ambient temperature		
• during operation / minimum	°C	-10
• during operation / maximum	°C	55
• during storage / minimum	°C	-25
• during storage / maximum	°C	70

Certificates

Certificate of suitability		
• as EC declaration of conformity		IEC 61010-1: 2001 (2nd Ed.) with Corr. 1, EN 61010-1: 2001 (2nd Ed.) and DIN EN 61010-1:2002 with "Berichtigung 1"
• as approval for Canada		UL 61010-1, 2nd Ed. CAN/CSA-C22.2 NO. 61010-1-04
• as approval for USA		UL 61010-1, 2nd Ed. CAN/CSA-C22.2 NO. 61010-1-04
• Approval Australia		Yes
• Approval Russia		Yes
Equipment marking / acc. to DIN EN 61346-2		P

General Product Approval	Declaration of Conformity	other
---------------------------------	----------------------------------	--------------



[sonstig](#)

[Bestätigungen](#)

other



Profibus

[PROFINET-Zertifizierung](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/7KM42120BA002AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/7KM42120BA002AA0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7KM42120BA002AA0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



~~RECHNUNG DER DIMENSIONEN~~

~~RECHNUNG DER DIMENSIONEN~~

last modified: 22.09.2015