


Bild / Picture

Anwendung / Application



USB zu 2x Seriell RS-232
mit 2.0 Meter Kabel (FTDI Chipset)



USB to 2x Serial RS-232 port
with 2.0 meter cable (FTDI chipset)

Beschreibung

Das USB zu RS-232 Kabel mit USB-A Stecker stellt zwei serielle RS-232 High Performance UART 16C550 Ausgänge zur Verfügung. Es wurde entwickelt, zwei weitere serielle Ausgänge für Notebook, PC, Workstation oder Server über den USB 1.1, 2.0 oder 3.2 Bus zu erweitern. Dank der einfachen Installation am USB-Port muss der Rechner nicht geöffnet werden und das Konverter-Kabel EX-13022 kann bei laufendem Betrieb installiert werden.

Description

The USB to RS-232 cable with USB-A connector provides two serial RS-232 high-performance UART 16C550 outputs. It was developed to expand two additional serial outputs for notebooks, PCs, workstations or servers via the USB 1.1, 2.0 or 3.2 bus. Thanks to its simple installation on the USB port, there is no need to open the computer and the EX-13022 converter cable can be installed during operation.

Merkmale

Features

Schnittstelle RS-232 V.24	Interface RS-232 V.24
16C550 FIFO Buffer mit 16Byte	16C550 FIFO Buffer with 16Byte
I/O Adressen und Interrupt werden vom Betriebssystem vergeben	I/O addresses and interrupt are assigned by the operating system
Daten Bits: 7 und 8	Data bits: 7 and 8
Stop Bits: 1, 1.5 und 2	Stop bits: 1, 1.5 and 2
Parity: none, even, odd, space und mark	Parity: none, even, odd, space and mark
Signale RS-232: TxD, RxD, RTS, CTS, DTR, DSR, DCD, GND	Signal RS-232: TxD, RxD, RTS, CTS, DTR, DSR, DCD, GND
Stromversorgung vom USB Bus (Bus Power)	Power from USB bus (Bus Power)

System / OS

Geprüft / Approved

Verpackung / Packaging



Spezifikation

Specification

Chip-Set:	FTDI	Chip-Set:	FTDI
Datentransfer-Rate:	300Baud bis 921.6KBaud	Data transfer rate:	300Baud up to 921.6KBaud
Anschlüsse:	1x USB A-Stecker Upstream 2x 9 Pin Seriell RS-232 Stecker	Connectors:	1x USB A-male Upstream connector 2x 9 pin serial RS-232 male connector
Hardwaresysteme:	USB 1.1, 2.0 oder 3.2 Gen 1	Hardware system:	USB 1.1, 2.0 or 3.2 Gen 1
Treiber:	Win98SE/ME/XP/200x/Vista/7/8/10/11 (32&64-Bit) Win Server 20xx/WinCE, Linux, MAC OS 10.x	Driver:	Win98SE/ME/XP/200x/Vista/7/8/10/11 (32&64-Bit) Win Server 20xx/WinCE, Linux, MAC OS 10.x
Betriebssysteme:	Gemäß Treiber	Operating systems:	According to driver
Betriebstemperatur :	0°C bis +55°C	Operating temperature :	32°F up to 131°F
Lagertemperatur:	-40°C bis +75°C	Storage temperature:	-40°F up to 167°F
Rel. Luftfeuchtigkeit:	5% bis 90%	Rel. Humidity:	5% to 90%
Stromversorgung:	Vom USB Port	Current Supply:	from the USB port
Abmessung:	Kabellänge 2.0 Meter	Size:	Cable length 2.0 meter
Gewicht:	130 g	Weight:	130 g
EAN:	4718359132216	EAN:	4718359132216
Ursprungsland:	China	Country of origin:	China
Lieferumfang:	EX-13022	Packaging contents:	EX-13022

Bilder / Pictures

