

1079591
<https://www.phoenixcontact.com/in/products/1079591>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 6, Pin, Push-in connection, 100 V, 20 A, 1.5 mm² ... 4 mm², with short-circuit function

Commercial data

Item number	1079591
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF7ACE
GTIN	4055626800387
Weight per piece (including packing)	33.4 g
Weight per piece (excluding packing)	30 g
Country of origin	CN

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

Technical data

Notes

General	Please observe the circuit diagram
General	Use at least 1.5 mm ² cables with a maximum conductor loop of 2 m. No open conductor loops permitted!
General	only use flexible conductors with ferrules

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

Product properties

Product type	Modular contact insert
Series	HC-M-TSC
Number of positions	6
Connection profile	6
Number of module slots	2
Contact material type	rolled

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection technology	Push-in connection
-----------------------	--------------------

Conductor connection

Conductor cross section	1.5 mm ² ... 4 mm ²
Connection cross section AWG	21 ... 12
Stripping length of the individual wire	8 mm

Dimensions

Dimensional drawing	
Width	33.8 mm
Height	45.8 mm
Length	29.2 mm

Mechanical characteristics

Contact diameter	4 mm
------------------	------

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

Electrical properties

Rated voltage (III/3)	100 V (when plugged in)
	100 V (Unplugged and during plugging)
Rated surge voltage	1.5 kV
Rated current	20 A (When plugged in)
	20 A (Unplugged and during plugging)

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC


Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--


Drawings

Diagram




Derating diagram (unmated)

Circuit diagram




Circuit diagram



Derating diagram (mated)

Dimensional drawing



Male insert

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

Classifications

ECLASS

ECLASS-11.0	27440205
ECLASS-13.0	27440205

ETIM

ETIM 9.0	EC000438
----------	----------

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

HC-TSC-M-06-PT-M - Contact insert module

1079591

<https://www.phoenixcontact.com/in/products/1079591>



Accessories

HC-CBU-MOD - Coding element

1636130

<https://www.phoenixcontact.com/in/products/1636130>



Coding socket for coding up to 16 connectors, for HC Modular

HC-CST-MOD - Coding element

1636127

<https://www.phoenixcontact.com/in/products/1636127>



Coding peg for coding up to 16 connectors, for HC Modular

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

HC-M-B06-MFH-B - Module carrier frame

1182085

<https://www.phoenixcontact.com/in/products/1182085>




Module carrier frame, size: B6, type : for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², application: Module carrier frame

HC-M-B10-MFH-B - Module carrier frame

1182088

<https://www.phoenixcontact.com/in/products/1182088>



Module carrier frame, size: B10, type : for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², application: Module carrier frame

HC-TSC-M-06-PT-M - Contact insert module

1079591

<https://www.phoenixcontact.com/in/products/1079591>



HC-M-B16-MFH-B - Module carrier frame

1182090

<https://www.phoenixcontact.com/in/products/1182090>

Module carrier frame, size: B16, type : for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², application: Module carrier frame



HC-M-B24-MFH-B - Module carrier frame

1182094

<https://www.phoenixcontact.com/in/products/1182094>

Module carrier frame, size: B24, type : for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², application: Module carrier frame



HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

HC-M-B06-MFH-H - Module carrier frame

1182087

<https://www.phoenixcontact.com/in/products/1182087>



Module carrier frame, size: B6, type : for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², application: Module carrier frame

HC-M-B10-MFH-H - Module carrier frame

1182089

<https://www.phoenixcontact.com/in/products/1182089>



Module carrier frame, size: B10, type : for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², application: Module carrier frame

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

HC-M-B16-MFH-H - Module carrier frame

1182093

<https://www.phoenixcontact.com/in/products/1182093>

Module carrier frame, size: B16, type : for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², application: Module carrier frame



HC-M-B24-MFH-H - Module carrier frame

1182095

<https://www.phoenixcontact.com/in/products/1182095>

Module carrier frame, size: B24, type : for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², application: Module carrier frame



HC-TSC-M-06-PT-M - Contact insert module

1079591

<https://www.phoenixcontact.com/in/products/1079591>



HC-TSC-M-06-PT-F - Contact insert module

1079590

<https://www.phoenixcontact.com/in/products/1079590>



Contact insert module, number of positions: 6, Socket, Push-in connection, 100 V, 20 A, 1.5 mm² ... 4 mm², with short-circuit function

CF CRIMPHANDY 0,5 - Crimping tool, electric

1212463

<https://www.phoenixcontact.com/in/products/1212463>



Mobile automatic stripping and crimping device, service tool, replacement part (waste guide plate), cutting tool (CUTFOX 12), on-tape ferrules

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

CF CRIMPHANDY 0,75 - Crimping tool, electric

1212464

<https://www.phoenixcontact.com/in/products/1212464>



Mobile automatic stripping and crimping device, service tool, replacement part (waste guide plate), cutting tool (CUTFOX 12), on-tape ferrules

CF CRIMPHANDY 1,0 - Crimping tool, electric

1212465

<https://www.phoenixcontact.com/in/products/1212465>



Mobile automatic stripping and crimping device, service tool, replacement part (waste guide plate), cutting tool (CUTFOX 12), on-tape ferrules

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

CF CRIMPHANDY 1,5 - Crimping tool, electric

1212466

<https://www.phoenixcontact.com/in/products/1212466>



Mobile automatic stripping and crimping device, service tool, replacement part (waste guide plate), cutting tool (CUTFOX 12), on-tape ferrules

CRIMPFOX 6 - Crimping pliers

1212034

<https://www.phoenixcontact.com/in/products/1212034>



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 6.0 mm², lateral entry, trapezoidal crimp

HC-TSC-M-06-PT-M - Contact insert module



1079591

<https://www.phoenixcontact.com/in/products/1079591>

CRIMPFOX CENTRUS 10S - Crimping pliers

1213154

<https://www.phoenixcontact.com/in/products/1213154>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 10 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

CRIMPFOX CENTRUS 6S - Crimping pliers

1213144

<https://www.phoenixcontact.com/in/products/1213144>



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in