

COMPACTA

2198PJI032P60-45,5X20

EAN 4031582418590



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Compacta
Type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Electric Conductive	No
Stainless	No
Load capacity Static	60 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	34 mm
Overall width	20 mm
Overall weight	0.03 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Angular
Housing Color	Blue passivated

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel Color	Silver grey (RAL7001)
Threadguards	Without threadguard
Diameter	32 mm
Tread width	15 mm
Body width	15 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	45.5 mm
Plate width	20 mm
Plate hole length (Maximum)	34.8 mm
Plate hole width (Maximum)	34.8 mm
Plate hole diameter	5.5 mm