

Torx Self Tapping Screw

Features

- No burrs and sharp edges
- Material: 1018~1022 carbon steel, heat treat HV 400~550
- Finish: Zinc / 3.8 µm min. with blue chromate
- Material and finish comply with 211/65/EU (RoHS)

Length	L
4	3.62~4.38
6	5.62~6.38
8	7.55~8.45
10	9.55~10.45
12	11.45~12.55
14	13.45~14.55
16	15.45~16.55
20	19.35~20.65
25	24.30~25.70
30	29.25~30.75

Thread (6g)	L	PART NO.
M3x1.35	12	RND 610-00620

Thread	D Head Diameter	H Head Height	Six-lobe Recess	S (Ref)	T Drive Depth	d
M3x1.35	5.30~5.60	2.26~2.40	T10	2.80	1.01~1.27	3.00~3.14

