



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 2

Terminal Block Connector Type: **Plug**

Connector System: **Wire-to-Board**

Centerline (Pitch): **5 mm [.197 in]**

Number of Rows: 1

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	2
Number of Rows	1
Wire Entry Angle	90°
Wire Entry Location	Side

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
Product Orientation	Right Angle



Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	12 A

Mechanical Attachment

Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M3
Connector Mounting Type	Board Mount

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5 mm[.197 in]

Dimensions

Wire Size	30 – 14 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Box
Packaging Quantity	300

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements:



Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1546931-2
2P UNSHROUD 5.0 HDR,HIGH TEMP



TE Part # 1546019-2
2 POS TERMI-BLOK PIN HEAD 180



TE Part # 282832-2
TERMI-BLOK PIN HEAD 180 2P. 5


Customers Also Bought



TE Part #1-1123723-2
3.96 EP HDR ASSY 2P(NATURAL)



TE Part #1721441-5
PCN-112D3MHZ,001B



TE Part #1744428-2
3.96 EP HDR ASSY 2P R/A, GW



TE Part #1744525-3
EP 03P RA-HDR ASY NO 2 PIN



TE Part #160101-2
RING TONGUE 20-16 AWG 0.0253
TPBR



TE Part #160018-2
RING TONGUE 176 20-16 AWG 0.251
NIBR



TE Part #2834010-3
SLIM CONTACT FOR WIRE 20-24AWG
NIBR



TE Part #1-1123724-2
3.96EP HDR ASSY 2(3)P NATURAL



TE Part #2834049-1
REC, 2P LATCHED POKE-IN WTW
CONN.NL



TE Part #2834048-1
PLUG, 2P LATCHED POKE-IN WTW
CONN.NL

Documents

Product Drawings

5MM PLUG,90/180,2 POS,GREEN,SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1546173-2_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1546173-2_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1546173-2_F.3d_stp.zip

English

3D PDF

English

Customer View Model

ENG_CVM_1546173-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_1546173-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_1546173-2_E.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English
1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications
Application Specification

English

Agency Approvals
UL

English