

Brush Cutter XGT®

UR013G

40Vmax, 0 – 3 500 / 6 700 min⁻¹

Model UR013G is a cordless brush cutter powered by 40Vmax XGT® Li-Ion battery

Feature and Benefits: High output power equivalent to that of 35 cc class engine model. Newly added "High-torque mode". Low noise level with offset bike handle and standard protector, designed for use with metal blade/ plastic blade/nylon cutting head.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	3500 - 6700 min ⁻¹
Cutting width	225 / 255 / 270 / 305 / 450 mm
Spindle Thread	M10 x 1,25 LH
Handle Type	U
Sound Power Level (L _{WA})	91,0 - 95,6 dB(A)
Sound Pressure Level (L _{pA})	77,3 - 81,4 dB(A)
Noise Uncertainty (K Factor)	1,5 - 2,1 dB(A)
Tool weight with battery	5,9 - 7,2 kg
Product Dimensions (L x W x H):	1922 x 690 x 546 mm
Nylon line- Diameter	2,7 mm
Brushless Motor	✓

User benefits

- Reverse switch for easy removal of grass clippings from the cutting tool
- Variable speed
- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Low noise level for pleasant work.

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing