

## Section 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**Product name:** JENOLITE FREEZE YOUR NUTS OFF

**Product code:** 88983

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

### 1.3. Details of the supplier of the safety data sheet

**Company name:** Jenolite UK Ltd  
Chater Lea Buildings  
Icknield Way  
Letchworth  
Herts  
UK  
SG6 1WT  
**Tel:** 01462 480764  
**Fax:** 01462 480765  
**Email:** Sales@jenolite.net

### 1.4. Emergency telephone number

**Emergency tel:** 01462 480764  
(office hours only)

## Section 2: Hazards identification

### 2.1. Classification of the substance or mixture

**Classification under CLP:** Eye Irrit. 2: H319; Flam. Aerosol 1: H222; -: H229

**Most important adverse effects:** Extremely flammable aerosol. Pressurised container: May burst if heated. Causes serious eye irritation.

### 2.2. Label elements

**Label elements:**

**Hazard statements:** H222: Extremely flammable aerosol.  
H229: Pressurised container: May burst if heated  
H319: Causes serious eye irritation.

**Hazard pictograms:** GHS02: Flame  
GHS07: Exclamation mark



# SAFETY DATA SHEET

JENOLITE FREEZE YOUR NUTS OFF

Page: 2

**Signal words:** Danger

**Precautionary statements:** P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P251: Do not pierce or burn, even after use.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

## 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

PROPAN-2-OL

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-661-7	67-63-0	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	1-10%

ACETONE - REACH registered number(s): 01-2119471330-XXXX

200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	1-10%
-----------	---------	---	---	-------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor. Move the exposed person to fresh air.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

[cont...]

**SAFETY DATA SHEET**  
JENOLITE FREEZE YOUR NUTS OFF

Page: 3

**4.3. Indication of any immediate medical attention and special treatment needed**

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

**Section 5: Fire-fighting measures**

**5.1. Extinguishing media**

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

**5.2. Special hazards arising from the substance or mixture**

**Exposure hazards:** In combustion emits toxic fumes.

**5.3. Advice for fire-fighters**

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

**Section 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

**6.2. Environmental precautions**

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

**6.3. Methods and material for containment and cleaning up**

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

**6.4. Reference to other sections**

**Reference to other sections:** Refer to section 8 of SDS.

**Section 7: Handling and storage**

**7.1. Precautions for safe handling**

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

**7.2. Conditions for safe storage, including any incompatibilities**

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed.

**Suitable packaging:** Must only be kept in original packaging.

**7.3. Specific end use(s)**

**Specific end use(s):** No data available.

[cont...]

**SAFETY DATA SHEET**  
JENOLITE FREEZE YOUR NUTS OFF

**Section 8: Exposure controls/personal protection**

**8.1. Control parameters**

**Hazardous ingredients:**

**PROPAN-2-OL**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	999 mg/m <sup>3</sup>	1250 mg/m <sup>3</sup>	-	-

**ACETONE**

UK	500ppm 1210mg/m <sup>3</sup>	1500ppm 3620mg/m <sup>3</sup>	-	-
----	------------------------------	-------------------------------	---	---

**DNEL/PNEC Values**

**Hazardous ingredients:**

**ACETONE**

Type	Exposure	Value	Population	Effect
DNEL	Dermal	186mg/kg/day	Workers	Systemic
DNEL	Inhalation	2420mg/m <sup>3</sup>	Workers	Local
DNEL	Inhalation	1210mg/m <sup>3</sup>	Workers	Systemic
DNEL	Oral	62mg/kg/day	Consumers	Systemic
DNEL	Dermal	62mg/m <sup>3</sup>	Consumers	Systemic
DNEL	Inhalation	200mg/m <sup>3</sup>	Consumers	Systemic
PNEC	Fresh water	10.6mg/l	-	-
PNEC	Marine water	1.06mg/l	-	-
PNEC	Fresh water	Intermittent release	-	-
PNEC	Fresh water sediments	30.4 mg/kg	-	-
PNEC	Marine sediments	3.04mg/kg	-	-
PNEC	Soil (agricultural)	29.5mg/kg	-	-
PNEC	Microorganisms in sewage treatment	100mg/l	-	-

**8.2. Exposure controls**

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Protective gloves. Chemically resistant gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

**Environmental:** Not applicable.

**SAFETY DATA SHEET**  
JENOLITE FREEZE YOUR NUTS OFF

Page: 5

**Section 9: Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

**State:** Aerosol

**Colour:** Colourless

**Odour:** Characteristic odour

**Solubility in water:** Insoluble

**Also soluble in:** Most organic solvents.

**Flash point°C:** -60

**Relative density:** 0.81

**9.2. Other information**

**Other information:** No data available.

**Section 10: Stability and reactivity**

**10.1. Reactivity**

**Reactivity:** Stable under recommended transport or storage conditions.

**10.2. Chemical stability**

**Chemical stability:** Stable under normal conditions.

**10.3. Possibility of hazardous reactions**

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

**10.4. Conditions to avoid**

**Conditions to avoid:** Heat.

**10.5. Incompatible materials**

**Materials to avoid:** Strong oxidising agents. Strong acids.

**10.6. Hazardous decomposition products**

**Haz. decomp. products:** In combustion emits toxic fumes.

**Section 11: Toxicological information**

**11.1. Information on toxicological effects**

**Hazardous ingredients:**

**PROPAN-2-OL**

IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg

[cont...]

**SAFETY DATA SHEET**  
JENOLITE FREEZE YOUR NUTS OFF

Page: 6

SCU	MUS	LDLO	6	gm/kg
-----	-----	------	---	-------

**ACETONE**

DERMAL	RAT	LD50	>7400	mg/kg
DERMAL	RBT	LD50	2000	mg/kg
ORAL	RAT	LD50	5800	mg/kg
VAPOURS	RAT	4H LC50	76000	mg/l

**Relevant hazards for product:**

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated

**Symptoms / routes of exposure**

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

**Other information:** Not applicable.

**Section 12: Ecological information**

**12.1. Toxicity**

**Hazardous ingredients:**

**ACETONE**

ALGAE	192H EC10	530	mg/l
Activated Sludge	30m EC10	1000	mg/l
DAPHNIA	48H EC50	8800	mg/l
Daphnia magna	192H EC10	2212	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	5540	mg/l

**12.2. Persistence and degradability**

**Persistence and degradability:** Biodegradable.

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** No bioaccumulation potential.

**12.4. Mobility in soil**

**Mobility:** Readily absorbed into soil.

[cont...]

**SAFETY DATA SHEET**  
JENOLITE FREEZE YOUR NUTS OFF

Page: 7

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

**12.6. Other adverse effects**

**Other adverse effects:** Negligible ecotoxicity.

**Section 13: Disposal considerations**

**13.1. Waste treatment methods**

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company. Dispose of contents and container according to national regulations.

**Recovery operations:** Not applicable.

**Disposal of packaging:** Not applicable.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**Section 14: Transport information**

**14.1. UN number**

**UN number:** UN1950

**14.2. UN proper shipping name**

**Shipping name:** ADR, ADN, IMDG - AEROSOLS  
IATA - AEROSOLS, flammable

**14.3. Transport hazard class(es)**

**Transport class:** 2.1

**14.4. Packing group**

**14.5. Environmental hazards**

**Environmentally hazardous:** No

**Marine pollutant:** No

**14.6. Special precautions for user**

**Special precautions:** Warning: Gases..

**Tunnel code:** D

**Transport category:** 2

[cont...]

# SAFETY DATA SHEET

JENOLITE FREEZE YOUR NUTS OFF

Page: 8

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

**Phrases used in s.2 and s.3:** EUH066: Repeated exposure may cause skin dryness or cracking.

H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H229: Pressurised container: May burst if heated

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product. Please note that due to the on-going change in regulation from CHIP to CLP any MSDS information supplied by Cedesa is only considered accurate at the time of its creation. During this time classifications of substances may change. Therefore it is possible that artwork and MSDS information may differ. As such if you have any concerns we recommend you request a new MSDS from us every 6-12 months.