

T494, Tantalum, MnO2 Tantalum, 47 uF, 10%, 35 VDC, SMD, MnO2, Molded, Low ESR, 500 mOhms, 7343, Height Max = 4.3mm



General Information

Supplier:	KEMET
Series:	T494
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, MnO2, Molded, Low ESR
Features:	Low ESR
RoHS:	Yes
Termination:	Tin
Shelf Life:	156 Weeks
MSL:	1

Dimensions

Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	4mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.6mm MIN
B	0.5mm +/-0.15mm
E	3.5mm REF
G	3.5mm REF
P	1.7mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Specifications

Capacitance:	47 uF
Capacitance Tolerance:	10%
Voltage DC:	35 VDC (85C), 23.45 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85°C
Dissipation Factor:	8.00% 120Hz 20C
Failure Rate:	N/A
Resistance:	0.5 Ohms (100kHz)
Ripple Current:	574 mAmps (100kHz 25C), 516.6 mAmps (85C), 229.6 mAmps (125C)
Leakage Current:	16.5 uA (5min 20C)

Packaging Specifications

Weight:	652.04 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500