



+  [View More](#)

PRODUCT NUMBER: 1015370

A800 Clear Hard Coat

Honeywell

Overview

Reference Number

1015370

Product Type

Eye and Face Protection

Range

Spectacles

Line

Single lens

Brand

Honeywell

Brand formerly known as

PULSAFE

Industry

- Administration

Product Use

General use and protection against impact (45m/s) Well suited for Indoor applications such as utilities, light & heavy manufacturing, bio tech, laboratories, clean rooms, ship building and automotive manufacturing

Feature

Protection that's easy on the eyes ... and the pocket Affordably priced and economical for

A800 Clear Hard Coat - 1015370

your business Slim profile Sporty styling

Features & Benefits

Benefit

Slim profile provides an ideal fit for workers with smaller faces. Sporty styling provides a fashionable fit

Feature

Temples feature and soft, padded inserts with extra flex built in

Benefit

It enhances sports styling and provides more comfort

Feature

Soft nosepiece conforms to various nose bridge shapes

Benefit

It gives added comfort and a non-slip fit

Feature

9-base polycarbonate abrasion resistant lenses

Benefit

They provide a 180° field of distortion-free vision

Technical Description

Shade Lens Color

Clear

Lens Coating

Hard Coat

Certifications

E.C. Declaration of Conformity

EC Category PPE

2

Quality Assurance

ISO 9001 / 2000

EC Certificate Number

EC 1790

EC Attestation

 EC Attestation



EC Attestation Number

EC 1790

We're sorry, there are no images available at this time.

EAN Code

7312550153703



EC TYPE-EXAMINATION CERTIFICATE: 1790

Product description: - Personal Protective Spectacles

Product identification: - HONEYWELL A800

Manufacturer: Sperian Eye and Face Protection Inc.
10 Thurber Boulevard
Smithfield
RI 02917
U S A

When assessed and examined against harmonised standard EN166:2001 are found to be in conformity with Council Directive 89/686/EEC and associated amendments, relating to personal protective equipment.

Authorised EU Representative: - Sperian Protection Europe (SAS)
ZI Paris Nord II
33 Rue des Vanesses, BP 50 288
95958 Roissy CDG cedex
France

Signed 

Date: 31st March 2008

K J Warren, Manager, Certification Services

For and on behalf of INSPEC International Ltd.
(Notified Body No: 0194)

certificate invalid
if not embossed

For terms and conditions of issue, see page 2

Terms and Conditions

Reference Documents: -

- | | | | |
|------|----------------|---|--|
| i) | Test Report | - | ICS T3141-01-1 Issue 1. |
| ii) | Technical File | - | TF/1790 |
| iii) | Quality Plan | - | Sperian Eye & Face Protection, Inc QP EN 166 |

Conditions attached to the issue of this certificate:

- i) Marking and instructions have been assessed in the English language only. It is the Manufacturers/Authorised Representatives responsibility to obtain and supply language versions acceptable to the country where the product is to be sold.
- ii) Any changes to the product, technical file or quality manual/quality plan shall be immediately notified to INSPEC.
- iii) The Manufacturer/Authorised Representative shall comply at all times with INSPEC's Regulations governing CE Product Certification.
- iv) This Certificate remains the property of INSPEC and may be withdrawn if any of the conditions attached to its issue are not complied with.
- v) This certificate may be copied or reproduced by the certificate holder, complete and without omissions or additions, and in accordance with INSPEC's terms of business.
- vi) This certificate has been provided in accordance with our standard Terms of Business, which can be viewed at, and printed from:

<http://inspec-international.com/ToB.pdf>

If you have difficulty accessing the Terms of Business, you may contact us for a copy.



CERTIFICATION INDEX

Item	Status	Issued	Amendment
Certificate, Pages 1 – 4	Withdrawn	31/03/08	Initial Issue
Certificate Pages 1 to 4	Valid	110930	Product name change to Honeywell

CERTIFICATION SCHEDULE

Model	Temple colour	Lens colour and coating	Optical Class	Lens Filter	Options
1015370	Clear	Clear w / HC	1	2C-1.2	F
1015369		Clear w / FOG-BAN	1	2C-1.2	F
1015368	Gray	TSR Gray w / HC	1	5-2.5	F
1015367		TSR Gray w / FOG-BAN	1	5-2.5	F
1015350		I/O Silver w / HC	1	5-1.7	F

All lenses are polycarbonate

Key:

F - Low energy impact

CERTIFICATION/TEST REPORT RECEIPT FORM

DATE RECEIVED: September 30, 2014

PRODUCT: Honeywell A800

CERTIFICATION TEST REPORT

SIGNATURES

Q.A. MANAGER: *John Pignard*

DIRECTOR QUALITY SYSTEMS: *Peter W. Bull*

DIRECTOR R & D: *Peter W. Bull*



E.C. Declaration of Conformity

The manufacturer or its legal representative supplier in the European Community:
Honeywell Safety Products Europe

Declares that the Personal Protective Equipment described here after conforms to the provisions of the European Council Directive 89/686/CEE:

Designation: A800 Clear Hard Coat
Reference: 1015370
Standard(s): EN166

This PPE is the object of the below EC examination certificate n°:
EC 1790

Delivered by:

INSPEC
56 Leslie Hough Way
Salford
M6 6AJ
Greater Manchester
United Kingdom
+44 (0)12 96 68 29 66

Drawn up in Manchester, on the 18/09/2014

By: K J Warren

Division: Eye and Face Protection

HONEYWELL SAFETY PRODUCTS EUROPE
Immeuble Edison - ZI Paris Nord II - 33 rue des Vanesses
BP 55288 Villepinte - 95958 ROISSY CDG CEDEX
SAS au capital 17 750 000 € - Siret 348 887 307 00137
Tel. +331 4990 7979 - Fax +331 4990 7980

ZI Paris Nord II 33, rue des Vanesses BP 50288 95958 Roissy CDG France

Tel: +33 (0) 49 90 79 79 Fax: +33 (0)1 49 90 79 80

www.honeywellsafety.com