

UC-WMC 4,4 (15X 5,5) BU - Conductor marker



0818849

<https://www.phoenixcontact.com/gb/products/0818849>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker, Sheet, blue, unlabeled, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, cable diameter range: 2.8 ... 4.4 mm, mounting type: clip on, Number of individual labels: 15, text field height: 5.5 mm, text field width: 15 mm

Your advantages

- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- The format automatically ensures printing with a high degree of positioning accuracy
- The markers support multi-line labeling
- One-handed mounting
- Two labeling areas that are clearly legible at all times
- Can be clipped on even after wiring has been completed
- The sheets provide space for including function texts
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	0818849
Packing unit	8 pc
Minimum order quantity	8 pc
Sales key	BG2217
Product key	BG2217
Catalog page	Page 196 (C-3-2019)
GTIN	4046356135214
Weight per piece (including packing)	11.713 g
Weight per piece (excluding packing)	6.5 g
Customs tariff number	39269097
Country of origin	PL

UC-WMC 4,4 (15X 5,5) BU - Conductor marker



0818849

<https://www.phoenixcontact.com/gb/products/0818849>

Technical data

Product properties

Product type	Conductor marking
Type	Card form

Marking

Number of individual labels	15
Number of individual labels per row	3
Identification technology	UV LED technology

Dimensions

Width	15 mm
Height	6.35 mm
Depth	6.6 mm

External dimensions

Outside diameter	2.8 mm ... 4.4 mm
------------------	-------------------

Text field

Text field width	15 mm
Text field height	5.5 mm

Material specifications

RoHS compliant	yes
Color	blue (RAL 5015)
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Cable/line

External cable diameter	2.8 mm ... 4.4 mm
-------------------------	-------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed

UC-WMC 4,4 (15X 5,5) BU - Conductor marker



0818849

<https://www.phoenixcontact.com/gb/products/0818849>

Test duration	96 h
---------------	------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Standards

Standards/regulations	EN 45545-2
-----------------------	------------

Mounting

Mounting type	clip on
---------------	---------

UC-WMC 4,4 (15X 5,5) BU - Conductor marker



0818849

<https://www.phoenixcontact.com/gb/products/0818849>

Classifications

ECLASS

ECLASS-13.0	27281102
-------------	----------

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UC-WMC 4,4 (15X 5,5) BU - Conductor marker



0818849
<https://www.phoenixcontact.com/gb/products/0818849>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk