

Miniature circuit breaker (MCB), Acti9 iC60L, 2P, 4A, MA curve, 20kA (IEC/EN 60947-2)

A9F90204

Main

Device application	Motor
Range	Acti9
product name	Acti9 iC60
Product or component type	Miniature circuit-breaker
Device short name	iC60L
Poles description	2P
Number of protected poles	2
[In] rated current	4 A
Network type	AC
Trip unit technology	Magnetic
Curve code	MA
Breaking capacity	15 kA lcu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 20 kA lcu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2 40 kA lcu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2
Utilisation category	Category A conforming to EN 60947-2 Category A conforming to IEC 60947-2
Suitability for isolation	Yes conforming to EN 60947-2 Yes conforming to IEC 60947-2
Standards	EN 60947-2 IEC 60947-2

Complementary

Network frequency	50/60 Hz	
Magnetic tripping limit	12 x In +/- 20 %	
[Ics] rated service breaking capacity	10 kA 50 % conforming to EN 60947-2 - 380415 V AC 50/60 Hz 7.5 kA 50 % conforming to EN 60947-2 - 440 V AC 50/60 Hz 10 kA 50 % conforming to IEC 60947-2 - 380415 V AC 50/60 Hz 7.5 kA 50 % conforming to IEC 60947-2 - 440 V AC 50/60 Hz 20 kA 50 % conforming to EN 60947-2 - 220240 V AC 50/60 Hz 20 kA 50 % conforming to IEC 60947-2 - 220240 V AC 50/60 Hz	
Limitation class	3 conforming to EN 60898-1 3 conforming to IEC 60898-1	
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN 60947-2 500 V AC 50/60 Hz conforming to IEC 60947-2	
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 60947-2 6 kV conforming to IEC 60947-2	
Contact position indicator	Yes	
Control type	Toggle	

Local signalling	Trip indicator
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	78.5 mm
Net weight	0.25 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Single terminal (top or bottom) 125 mm² rigid Single terminal (top or bottom) 116 mm² flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Separate block

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP20 conforming to EN 60529
Pollution degree	3 conforming to EN 60947-2 3 conforming to IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	02000 m
Ambient air temperature for operation	-3570 °C
Ambient air temperature for storage	-4085 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.2 cm
Package 1 Length	9.3 cm
Package 1 Weight	219.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	7.7 cm
Package 2 Width	9.7 cm
Package 2 Length	22.1 cm

Package 2 Weight	1.391 kg
Unit Type of Package 3	S03
Number of Units in Package 3	66
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	15.789 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	9
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	C839c050-8547-41ce-b0db-e9813554fc09
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins