



DELTA i-system electrical white Time switch, 16A 250V, 2-pole with cover plate 55x 55 mm can be switched off, runtime up to 15 min

Model		
product brand name		SETRON
design of the switching function		off 2-pole
type of composition		basic element with central cover plates
General technical data		
surface processing		other
material		thermoset
operating voltage rated value		250 V
Protection class		
protection class IP		IP20
Breaking Capacity		
switching capacity current		16 A
Dissipation		
power loss [W] for rated value of the current at AC in hot operating state per pole		3 500 W
Main circuit		
operational current rated value		16 A
Adjustable parameters		
adjustable time		
• initial value		0.5 min
• full-scale value		15 min
Appearance		
appearance		polished
RAL color number		RAL 1013
color		white
Product details		
number of NC contacts		0
number of NO contacts		2
number of CO contacts		0
product feature		
• halogen-free		Yes
• transparent		No
Mechanical Design		
fastening method		flush mounting
net weight		177 g
material of the enclosure		plastic
Approvals Certificates		
General Product Approval	other	Environment

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT1012>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT1012>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT1012

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

5/26/2025

