

FEATURES

- **Graphite material:** Offers excellent thermal resistance and durability
- **Maximum operating temperature of 650°C:** Suitable for high-temperature applications
- **Maximum operating pressure of 20000 kPa:** Ensures reliable performance under high pressure
- **Rotary speed of 30 m/s:** Capable of handling high-speed applications
- **6.5 mm section:** Provides a robust seal for various industrial uses

RS PRO 8m Graphite Gland Packing, 6.5mm Section

RS Stock No: 606-571



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for high-performance sealing in industrial applications. Made from durable graphite, it provides excellent resistance to high temperatures and pressures, making it ideal for demanding environments. With a maximum operating temperature of 650°C and pressure of 20000 kPa, this gland packing ensures reliable sealing in a variety of settings.

General Specifications

Maximum Operating Pressure	20000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	30 m/s
Section	6.5 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Graphite

Operation Environment Specifications

Maximum Operating Temperature	650 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------