

Northbrook, Illinois • (847) 272-8800
 Melville, New York • (631) 271-6200
 Santa Clara, California • (408) 985-24
 Research Triangle Park,
 North Carolina • (919) 549-1400
 Camas, Washington • (360) 817-5500



CHERRY ELECTRICAL PRODUCTS CORP
 MR T GILMORE
 11200 88TH AVE
 PLEASANT PRAIRIE WI 53158

RE: Project Number(s) - 02NK24640

Your most recent Certification is shown below. You may also view this information, or a portion of this information (depending on the product category), on UL's Online Certifications Directory at www.ul.com/database. Please review the text and contact the Conformity Assessment Services staff member who handled your project if revisions are required. For instructions on placing an order for this information in a 3 x 5-inch format, you may refer to the enclosed order form for UL Card Service.

WOYR2
 Switches, Special Use - Component

July 19, 2002

CHERRY ELECTRICAL PRODUCTS CORP
 11200 88TH AVE, PLEASANT PRAIRIE WI 53158

E23301

Cat. No.	Amps	V	Frequency	HP
A23* w w/o	Pole 1: 5	125-250	50 or 60	1/4
prefix letter	Pole 2: 10	125-250	50 or 60	1/2
A24 w w/o	0.1	125	60	—
prefix letter				
A25 w w/o	Pole 1: 01	125	60	—
prefix letter	Pole 2: 5	125-250	60	1/4
A26 w w/o	Pole 1: 01	125	60	—
prefix letter	Pole 2: 10	125-250	60	1/2
A27 w w/o prefix letter	Pole 1: 5	125-250	60	1/4
	Pole 2: 10	125-250	60	1/2
A28 w w/o prefix letter	Pole 1: 10	125-250	50 or 60	1/2
	Pole 2: 10	125-250	50 or 60	1/2
A29 w w/o prefix letter	10	125-250	50 or 60	1/2
C10 f/b -31EA, -35EA, -36EA, -42A or -46A	0.15	125	60	—
C10-62D or -75E	0.1	125	60	—
D3A4	6(L)	125	60	—
D3B	10	125/250	60	1/2
C10-62D or -75E	0.1	125	60	—
D3A4	6(L)	125	60	—
D3B	10	125/250	60	1/2
D36	4	250	60	—
D364	4	250	60	—

Underwriters Laboratories Inc.®

Cat. No.	Amps	V	Frequency	HP
RS3A-A f/b by additional suffixes	16/8	125/250	60	—
	6	30	DC	—
RS3A-B f/b additional suffixes	16/8	125/250	60	—
	6	30	DC	—
RS3A-E f/b additional suffixes	16/8	125/250	60	—
	6	30	DC	—
RS3B-A f/b additional suffixes	0.1	250	60	—
	0.3	30	DC	—
RS3B-B f/b additional suffixes	0.1	250	60	—
	0.3	30	DC	—
RS3B-E f/b additional suffixes	0.1	250	60	—
	0.3	30	DC	—
RS3C-A f/b additional suffixes	Pole 1: 16/8	125/250	60	—
	6	30	DC	—
	Pole 2: 0.1	250	60	—
	0.3	30	DC	—
RS5	Circuit 1-2, 5-6:	250	60	—
	16			
f/b additional suffixes	6	30	DC	—
	Circuit 3-4: 0.1	250	60	—
	0.3	30	DC	—
RS4A f/b additional suffixes	Corciot 1-2:160.3 circuit 3-4:0.3	250	60	—
	30		DC	—
RS4B f/b additional suffixes	Circuit 1-2:0.3 Circuit 3-4:16	30	DC	—
	250		60	—
WR	16	125/250	60	1/4
	6.9	250	60	3/4
	20	125	60	
TR	16	125/250	60	1/4
	6.9	250	60	3/4
	20	125	60	
GR	12	125/250	60	—
SR	10	125	60	—
	6	250	60	—
	6	125	60	—
	3	250	60	—
LR	10/8	125/250	60	1/4
CR	20/16	125/250	60	—
	6	120VL	60	—
	—	250	60	3/4

*Followed by -00 thru -99, followed by one or more letters, the first of which is not S.

**With or without -00 thru -99, followed by one or more letters, the first of which is not S.

Marking: Company name, electrical rating and UL Recognized Component Mark on switch. Catalog designation on switch or smallest container.