

CUSTOMER	CLASS	FILE
Arcoelectric Limited 61 Central Ave West Molesey Surrey KT8 2RF United Kingdom	6241-10 SWITCHES-Snap - Special Use	010990_0_000
<b>Refer to Class Description for program details</b>		

- 1250 Rocker Switches: single and double pole rocker switches, 16A, 250V ac resistive, 10A, 250V ac, 1A, 30V dc and 1/2 hp, 125V ac. See note 1.
- 1300 Rocker Switches: 1300 - single pole ON/OFF, 1330, 1350 - double pole ON/OFF, 1353 - double pole ON/OFF illuminated, 20A, 250V ac, 1 hp, 250V ac and 1/2 hp, 125V ac. See note 1.
- 1400/1500 Rocker Switches: 1400/1500 - single pole ON/OFF, 1330, 410/1510 - single pole 2 position changeover, 1450/1550 - double pole ON/OFF, 1460/1560 - double pole 2 position changeover, 1453/1553 - 1401/1501 - single pole ON/OFF biased to ON, 1411/1511 - single pole 2 position changeover biased, 1421/1521 - single pole 3 position changeover biased to centre from one end, 1422/1522 - single pole 3 position changeover biased to centre from both ends, 1451/1551 - double pole ON/OFF biased to OFF, 1452/1552 - double pole biased to ON, 1461/1561 - double pole 2 position changeover biased, 1563/1564 - one pole changeover, one pole ON/OFF, 1471/1571 - double pole 3 position changeover biased to centre from one end, 1472/1572 - double pole 3 position changeover biased to centre from both ends, 16A, 250V ac, 1420/1520 - single pole 3 position changeover, 1470/1570 - double pole 3 position changeover, 16A, 250V ac, 1/2 hp, 250V ac, 1/4 hp, 125V ac. See note 1.
- 1700 Lever Switches: 1700 - single pole ON/OFF, 1710 - single pole 2 position changeover, 20A, 250V ac res, 1 hp, 250V ac, 1/2 hp, 125V ac. 1720 - single pole 3 position changeover, 20A, 250V ac res, 1/2 hp, 250V ac, 1/4 hp, 125V ac. 1750 - double pole ON/OFF, 1760 - double pole 2 position changeover, 16A, 250V ac res, 1 hp, 250V ac, 1/2 hp, 125V ac.
- 1700 Lever Switches: 1770 - double pole 3 position changeover, 16A, 250V ac res, 1/2 hp, 250V ac, 1/4 hp, 125V ac. 1784-1789 - double pole bodies housing single pole circuits, 5A, 250V res. See note 1.
- 2000 Series Slide Switches: Single and double pole variants in 2 to 5 position types with various actuators and body styles. 16A, 250V ac; 4A, 300V ac.
- 3100 Series Door Switches: 3101 - single pole push to make, 3102 - single pole push to break, 3111 - single pole push to changeover, 5A, 250V ac.
- 5400/5500 Series Rocker Switches: 5400/5500 - single pole ON/OFF, 5403/5503 - single pole illuminated, 5405/5505 - single pole ON/OFF with auxiliary contact, 5408/5508 - single pole illuminated with permanent neutral to neon, 16A, 250V ac res, 15A, 250V ac, 1 hp, 250V ac, 1/2 hp, 125V ac. 5550 - double pole ON/OFF, 5551 - double pole biased to OFF, 5552 - double pole isolated illumination biased to OFF, 5553 - double pole ON/OFF illuminated, 5554 - double pole ON/OFF illuminated biased to OFF, 5555 - single pole ON/OFF illuminated biased, 5556 - single pole isolated light, 5557 - double pole ON/OFF isolated light, 5558 - single pole ON/OFF illuminated, 5559 - single pole isolated light biased to OFF, 5560 - double pole 2 position changeover, 5562 - 2 single pole ON/OFF reversed, 5564 - one pole ON/OFF one pole changeover, 5566 - single pole changeover isolated light, 5568 - one pole changeover one pole ON/OFF illuminated, 5590 - one pole ON/OFF one pole ON/OFF illuminated, 5591 - one pole ON/OFF one pole ON/OFF illuminated biased to OFF, 5592 - one pole ON/OFF one pole 2 position changeover illuminated, 15A, 250V ac. See note 1.
- Rocker Switch, Series 60..XX, s.p.s.t., d.p.d.t., illuminated or not, ON/OFF-changeover, rated 20A, 277V ac; 1/2Hp, 125V ac; 1Hp, 277V ac.
- 7000 Series Push Button Switches: 7000 - single pole ON/OFF alternate, 7001 - single pole ON/OFF momentary, 7003 - single pole ON/OFF illuminated alternate, 7004 - single pole ON/OFF illuminated momentary, 7050 - double pole ON/OFF alternate, 7051 - double pole ON/OFF momentary, 7053 - double pole ON/OFF illuminated alternate, 7054 - double pole ON/OFF illuminated momentary, 16A, 250V ac res, 1 hp, 250V ac, 1/2 hp, 125V ac. See note 1.
- Push button switches, single pole, alternate action, momentary action, illuminated, non-illuminated, rated: 8350, 8353, 8354, 8200, 8201, 8250, 8251, 12A @ 250V ac, 1hp @ 250V ac, 1/2hp @ 125V ac; 8300, 8301, 8303, 8304, 13A, 250v ac, 1hp, 250V ac, 1/2hp, 125V ac.

Note: Model designation may have prefix and suffix letters.

- 8500 Series Rocker Switches: 8500 - single pole ON/OFF, 8503 - single pole ON/OFF illuminated, 8550 - double pole ON/OFF, 8553 - double pole ON/OFF illuminated, 15A, 250V ac res, 14A, 250V ac, 10A, 277V ac, 1/2 hp, 250V ac, 1/4 hp, 125V ac.
- 8600 Series Rocker Switches:
  - 8600 - 1 pole, ON/OFF, 16A, 250V ac, 1/2hp, 277V ac, 1/4hp, 125V ac;
  - 8601 - 1 pole, ON/OFF biased to OFF, 8602 - 1 pole ON/OFF biased to ON: 6A, 277V ac, 16A, 250V ac;
  - 8610 - 1 pole 2 positions, changeover, 8650 - 2 poles, 2 positions changeover: 10A, 277V ac, 1/2hp, 277V ac, 1/4hp, 125V ac;
  - 8611 - 1 pole 2 positions changeover biased, 8651 - 2 poles ON/OFF biased to OFF, 8652 - 2 poles ON/OFF biased to ON, 8653 - 2 poles ON/OFF illuminated, 8661 - 2 poles, 2 positions changeover biased, 6A, 277V ac;
  - 8620 - 1 pole, 3 positions, changeover, 15A, 277V ac, 1/2hp, 277V ac, 1/4hp, 125V ac;
  - 8670 - 2 poles 3 positions, 8671 - 2 poles, 3 positions changeover, biased to center from one end, 8672 - 2 poles, 3 positions, changeover biased from both ends to center, 10A, 277V ac, 1/2hp, 125/277V ac.
- 9000 Series Rotary Switch: 9000 - up to 4 positions and 4 terminals, 2A, 250V ac.
- 9XYY Series Rotary Switch where X = 2 to 6 to indicate no of indexes.
- YY from 00 to 99 = build up of the switch 277V ac, 20A, 277V ac N.I.; 2 hp 250V ac; 1 hp, 125V ac.

Note:

1. Prefix letters are added to indicate the different terminal options and suffix letters indicate cosmetic actuator and body variants.

- Toggle Switches, :
  - Series 3900, 3950: (spst or dpst), 20A @ 277V ac, 1hp@ 250Vac, 1/2hp@ 125V, 7A @72Vdc, 14A @ 36Vdc,;
  - Series 3901, 3902, 3920, 3921, 3922: (spst), 16A @ 277V ac, 1hp@ 250Vac, 7A @72Vdc, 14A @ 36Vdc,;
  - Series 3910, 3911, 3951, 3952, 3960, 3961, 3970, 3971, 3972: (spst or dpst or dpdt or dp3t), 16A @ 277V ac, 1hp@ 250Vac, 7A @72Vdc, 14A @ 36Vdc,;

Note: Model designation may have prefix and suffix letters.

/pg