




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 26236680460) Decamethylcyclopentasiloxane (D5) (.5% in 26236680460) Octamethylcyclotetrasiloxane (D4) (.5% in 26236680460) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on





requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1452408-2 SECONDARY LOCK FOR 58 POS CONN	 TE Part # 1452409-2 SECONDARY LOCK FOR 58 POS CONN	 TE Part # CAT-AM705-T273 AMP MCP, RECEPTACLE AND TAB	 TE Part # 828904-1 SINGLE WIRE SEAL FOR J.P.T.CON
 TE Part # 1-1452424-2 BLIND PLUG FOR MCON 1.2 CB (1.	 TE Part # 1452416-1 58POS CONNECTOR COVER 180 ASSY	 TE Part # 828905-1 SINGLE-WIRE-SEAL(5MM HOLE)	 TE Part # CAT-M4595-T273 MCON Receptacle and Tab
 TE Part # 828922-1 2,5MM CAVITY PLUG FOR 5,4MM DI	 TE Part # 1-1452424-1 BLIND PLUG FOR MCON 1.2 CB (0,	 TE Part # 1452421-1 58 POS. CONNECTOR COVER 90 ASSY	

Customers Also Bought

 TE Part #184002-1 2 POS. PLUG ASSY, KEY B, GRAY	 TE Part #1670144-3 MCON 1.2 CB REC SRC AG	 TE Part #2-1393366-2 GET-SOCKET TERMINAL, SILVER VE	 TE Part #330367 SPLICE,SOLIS BUTT 22-16
--	--	--	--



TE Part #829131P012

ES2000-NO.1-C1-0-50MM



TE Part #330368

SPLICE,SOLIS BUTT 16-14



TE Part #184032-1

3 POS. PLUG ASSY, KEY A



TE Part #1-1924067-9

2POS, MCON 1.2 CB REC 2p TL SEALED



TE Part #3-1438136-4

70 WAY PCM HARNESS ASSY

TE Part #5-1437843-8

103092=7-1437843-9 BLACK

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1564285-9_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1564285-9_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1564285-9_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English