



Image may differ from product. See technical specification for details.

PBMF 607560 M1G1

Solid bronze flanged bushing

SKF solid bronze flanged bushings are suitable for oscillating, rotating and linear movements, and can accommodate radial loads as well as axial loads in one direction. They are designed for a wide variety of operating conditions and applications in tough environments.

- Insensitive to dirty environments
- Resistant to impact loads and vibrations at low speeds
- Operate with lower quality shaft finish
- Good corrosion resistance

Overview

Dimensions

Bore diameter	60 mm
Outside diameter	75 mm
Width	60 mm
Flange diameter	85 mm
Flange thickness	8 mm

Properties


Design	Flanged
Material	Solid bronze
Relubrication feature	With

Logistics

Product net weight	0.924 kg
eClass code	23-05-01-90
UNSPSC code	31171605

Technical specification

Material	Solid bronze
Operating temperature	min. -40 °C
Operating temperature	max. 250 °C



Dimensions

d	60 mm	Bore diameter
D	75 mm	Outside diameter
B	60 mm	Width
D_1	85 mm	Outside diameter flange
B_1	8 mm	Width flange
a	3 mm	Distance side face - axial lubrication groove
h	61.5 mm	Distance bottom axial lubrication groove - opposite bore diameter
α	124 °	Aperture angle axial lubrication groove

Recommended fits

Tolerance shaft	e7
Tolerance housing	H7

Calculation data

Specific dynamic load factor	K	25 N/mm ²
Specific static load factor	K ₀	45 N/mm ²
Permissible sliding velocity	v	max. 0.5 m/s
Coefficient of friction	μ	min. 0.08
Coefficient of friction	μ	max. 0.15



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.