

TECHNICAL DATA

Fluke 700LTP-1 Low-pressure Test Pump



Key features

- Pump can be easily cleaned without disassembly
- Adjustable pressure relief valve with slow-bleed capability. Allows the slow release pressure at a controlled rate
- Quick fit connectors, one for the reference port for connection to a Fluke 700 series pressure module and one to connect to a unit under test
- Slim design, easy to carry and use

Product overview: Fluke 700LTP-1 Low-pressure Test Pump

The Fluke 700LTP-1 is a hand operated pressure pump designed to generate either vacuum to -12.7 PSI / -.87 bar or pressures to 100 psi / 6.9 bar. The Fluke 700LTP-1 has two pressure ports with quick fit connectors. Test hoses are terminated with 1/8-NPT female fittings that can be adapted using the BSP/ISO adapters.

For use with 700 series pressure modules and 717 pressure calibrators. Ideal for low pressure applications requiring accurate low pressure testing.

Specifications: Fluke 700LTP-1 Low-pressure Test Pump

Mechanical and General Specifications



Size (L x W x D)	5.9 x 4 x 1.25 in (150 x 100 x 32 mm)
Weight	226 g or .5 lbs (pump only)
Warranty	One year
Material	Exposed Materials: Aluminum, silicon, neoprene, stainless steel, Buna-N

Ordering information



700LTP-1

Low-pressure Test Pump

Part#: 2811763

UPC#: 095969397704

-
- (2) adapters to convert the reference and UUT port hose fitting to 1/4" BSP female
 - One seal kit
 - Instruction sheet in English
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2026 Fluke Corporation.
Specifications subject to change without notice.
07/2026

**Modification of this document is not permitted
without written permission from Fluke
Corporation.**