



Connectors > Rectangular Connectors > Standard Rectangular Connectors > STD Temp GRACE INERTIA Cap



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Mating Alignment: **With**

Mating Alignment Type: **Keyed**

Mating Retention: **Without**

[All STD Temp GRACE INERTIA Cap \(24\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Connector & Keying Code	A
-------------------------	---



Primary Product Color	Natural
Contact Features	
Contact Layout	Inline
Contact Base Material	Copper Alloy
Contact Type	Tab
Contact Retention Within Housing	Without
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
Strain Relief	Without
Panel Mount Feature	Without
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	Without
Mating Retention Type	Inertia Locking, Latch
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Housing Material	Nylon 66
Centerline (Pitch)	6.2 mm[.244 in]
Dimensions	
Connector Height	11.7 mm[.46 in]
Connector Length	20.4 mm[.802 in]
Usage Conditions	
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Industry Standards	
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	400



Packaging Method

Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-G7534-T111
GRACE INERTIA Tab



TE Part # 1747995-2
GHC EYELET 6.2 3POS PLUG
HOUSING RED



TE Part # CAT-G7534-R2435
GRACE INERTIA Receptacle




TE Part # CAT-G7534-P729
STD Temp GRACE INERTIA Plug

Also in the Series | GRACE INERTIA 6.2



Connector Contacts(4)



Connector Hardware(1)



Power Contacts(4)



Rectangular Connector Housings(13)




Rectangular Power Connectors(13)




Standard Rectangular Connectors(13)

Customers Also Bought



TE Part #170340-3
FF 250 TAB 20-14AWG PTBR
WITHOUT LATCH



TE Part #179975-1
250 PL EX REC. 15-10AWG PTBR



TE Part #2379907-1
250 HSG REC. F-SPRING 10MM 8MM
3P NAT.



TE Part #179464-1
POWER DBL LOCK CAP HSG F/H 3P




TE Part #2358709-2
250 FAST,TAB,TAPING AND REEL
ASSY PODLOK




TE Part #1-1903414-2
GHC 9.0 3POS PLUG HSG RED



TE Part #2379911-1
250 FSPRING REC. 18-14AWG TPBR



TE Part #1746971-1
GRACE INERTIA CONNECTOR 6.2
MM PITCH REC



TE Part #939691-1
CRIMPER LUBRICAN OIL



TE Part #4-1903414-2
GHC 9.0 3POS PLUG HSG BLACK

Documents



Product Drawings

GRACE INERTIA 6.2mm PITCH CAP 3POS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1746978-1_C3.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1746978-1_C3.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1746978-1_C3.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773883-5 GRACE INERTIA connector quick reference guide

English

Product Specifications

Application Specification

English

Instruction Sheets

Extraction Tool For Grace Inertia Connector

Japanese

Instruction Sheet (non U.S.)

Japanese