


Geberit Mapress Stainless Steel cap



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5
- For grey and black water with a pH value ≥ 5.5

- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding
- For permanent termination of pipe ends

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	L cm	Z cm
33212	12	15	2.3	0.3
33213	15	18	2.3	0.3
33214	20	22	2.4	0.3

Art. no.	DN	d _ø mm	L cm	z cm
33215	25	28	2.6	0.3
33216	32	35	2.9	0.3
33217	40	42	3.3	0.3
33218	50	54	3.8	0.3
33219	65	76.1	6	0.7
33220	80	88.9	6.7	0.7
33221	100	108	8.2	0.7