

# Product datasheet

Specifications



## adaptation kit for motor/gear-box combination

GBK0800852S

EAN Code: 3606480397820

### Main

Range compatibility	Lexium ILS Lexium SD3
Product or component type	Adaptation kit
Device short name	GBK
Accessory / separate part category	Adaptation accessory
Product compatibility	BRS3 ILS
Accessory / separate part destination	For assembly motor and gearbox
Kit composition	An adaptor plate Screws and bolts for mounting A shaft end adaptor
Gearbox external diameter	80 mm

### Complementary

Motor flange size	85 mm
Number of motor stacks	1 2
Length	21.2 mm
Net weight	0.45 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.400 cm
Package 1 Width	16.300 cm
Package 1 Length	17.700 cm
Package 1 Weight	436.000 g

### Logistical informations

Country of origin	DE
-------------------	----

### Contractual warranty

Warranty (in months)	18
----------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number

7c9e597c-8ccc-4daf-95fb-5d67fc70d561

REACH Regulation

[REACH Declaration](#)

PVC free

Yes

## Use Again

### Repack and remanufacture

End of life manual availability


No need of specific recycling operations

Take-back

No

Dimensions Drawings

Dimensions



(1) Gearbox

Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a	c	Ø6	Ø7	Ø8 (outer diameter x inner diameter x length)
21.2	85	M6	99	19 x 12 x 26

Values in in.

a	c	Ø6	Ø7	Ø8 (outer diameter x inner diameter x length)
0.83	3.35	M6	3.90	0.74 x 0.47 x 1.02