



**Part Number :** [351510414](#)

**Product Description :** VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue

**Series Number :** 35151

**Status :** Active

**Product Category :** Connector Housings



---

## Documents & Resources

### Drawings

[351510414 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[351500000AS ENG-000.pdf](#)

[351500000AS KOR-000.pdf](#)


[PK-35151-005-001.pdf](#)

[PS-35150-003-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	35151
Description	VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	800754834728

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	4
Color - Resin	Blue
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes

Material - Resin	PBT
Net Weight	3.746/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	<u>2026500909</u>
VersaBlade Hybrid Receptacles Housings and TPAs	<u>35150</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<u>35524</u>

### Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural	<u>351500290</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red	<u>351500292</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow	<u>351500293</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue	<u>351500294</u>

VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	<u>2270288400</u>
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	<u>2270298400</u>
VersaBlade Male Crimp Terminals	<u>35745</u>
VersaBlade Female Crimp Terminals	<u>35746</u>
VersaBlade Male Crimp Terminals	<u>35747</u>
VersaBlade Female Crimp Terminals	<u>35748</u>