



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00	Z1	ECO-14-010907	25AUG2014	KR OC

D	YES	DIM A	NO. OF CIRCUITS	PART NO.
	YES	71.12[2.800]	28	5-640442-8
	YES	68.58[2.700]	27	5-640442-7
	YES	66.04[2.600]	26	5-640442-6
	YES	63.50[2.500]	25	5-640442-5
	YES	60.96[2.400]	24	5-640442-4
	YES	58.42[2.300]	23	5-640442-3
	YES	55.88[2.200]	22	5-640442-2
	YES	53.34[2.100]	21	5-640442-1
	YES	50.80[2.000]	20	5-640442-0
	YES	48.26[1.900]	19	4-640442-9
	YES	45.72[1.800]	18	4-640442-8
	YES	43.18[1.700]	17	4-640442-7
	YES	40.64[1.600]	16	4-640442-6
	YES	38.10[1.500]	15	4-640442-5
	YES	35.56[1.400]	14	4-640442-4
	YES	33.02[1.300]	13	4-640442-3
	YES	30.48[1.200]	12	4-640442-2
	YES	27.94[1.100]	11	4-640442-1
	YES	25.40[1.000]	10	4-640442-0
	YES	22.86[.900]	9	3-640442-9
	YES	20.32[.800]	8	3-640442-8
	YES	17.78[.700]	7	3-640442-7
	YES	15.24[.600]	6	3-640442-6
	YES	12.70[.500]	5	3-640442-5
	YES	10.16[.400]	4	3-640442-4
	YES	7.62[.300]	3	3-640442-3
	YES	5.08[.200]	2	3-640442-2

NO	71.12[2.800]	28	2-640442-8	SUPERCEDED BY 5-640442-8
NO	68.58[2.700]	27	2-640442-7	SUPERCEDED BY 5-640442-7
NO	66.04[2.600]	26	2-640442-6	SUPERCEDED BY 5-640442-6
NO	63.50[2.500]	25	2-640442-5	SUPERCEDED BY 5-640442-5
NO	60.96[2.400]	24	2-640442-4	SUPERCEDED BY 5-640442-4
NO	58.42[2.300]	23	2-640442-3	SUPERCEDED BY 5-640442-3
NO	55.88[2.200]	22	2-640442-2	SUPERCEDED BY 5-640442-2
NO	53.34[2.100]	21	2-640442-1	SUPERCEDED BY 5-640442-1
NO	50.80[2.000]	20	2-640442-0	SUPERCEDED BY 5-640442-0
NO	48.26[1.900]	19	1-640442-9	SUPERCEDED BY 4-640442-9
NO	45.72[1.800]	18	1-640442-8	OBSELETE
NO	43.18[1.700]	17	1-640442-7	
NO	40.64[1.600]	16	1-640442-6	
NO	38.10[1.500]	15	1-640442-5	
NO	35.56[1.400]	14	1-640442-4	
NO	33.02[1.300]	13	1-640442-3	
NO	30.48[1.200]	12	1-640442-2	
NO	27.94[1.100]	11	1-640442-1	SUPERCEDED BY 4-640442-1
NO	25.40[1.000]	10	1-640442-0	
NO	22.86[.900]	9	640442-9	
NO	20.32[.800]	8	640442-8	
NO	17.78[.700]	7	640442-7	
NO	15.24[.600]	6	640442-6	
NO	12.70[.500]	5	640442-5	
NO	10.16[.400]	4	640442-4	
NO	7.62[.300]	3	640442-3	
NO	5.08[.200]	2	640442-2	

- 1 MATERIAL: CONNECTOR - NYLON UL94V-2 (BLUE).
CONTACTS - 0.30[.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
FOR 640442-2 THRU 2-640442-8.
MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS
OVER NICKEL UNDERPLATE FOR 3-640442-2 THRU 5-640442-8.
- 2 CONTACTS ACCEPT 26 AWG WIRE WITH 1.52[.060] MAX
INSULATION DIAMETER.
- 3 CONTACTS MUST ACCEPT 0.64±0.03[.025±.001]
POST AND REMAIN LOCKED IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY
NOT APPEAR ON ALL ASSEMBLIES.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 10JUN2003		
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 10JUN2003		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BOSSI 10JUN2003	NAME MTA 100 CONNECTOR ASSEMBLY, 26 AWG, STANDARD	
0 PLC ±		PRODUCT SPEC 108-1050	SIZE A2	
1 PLC ±		APPLICATION SPEC 114-1019	CAGE CODE 00779	DRAWING NO C=640442
2 PLC ±		WEIGHT	RESTRICTED TO	
3 PLC ± 0.13 [.005]		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 of 1
4 PLC ±			REV Z1	
ANGLES ±				
FINISH				