



Passive Components > Resistors > Through-Hole Resistors > Wirewound Resistor: Vertical Mount



Resistance Value: 100 Ω

Resistor Type: Power Resistor

Element Type: Wire Wound

Power Rating: 4 W

Resistance Class: Up to 1kΩ

[All Wirewound Resistor: Vertical Mount \(166\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Value	100 Ω
Power Rating	4 W
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	20 x 7 x 8 mm
------------------------------	---------------



Usage Conditions

Operating Temperature Range	-55 – 350 °C
Temperature Coefficient	±200 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SBCHE4100RJ

100 ohm, Through-Hole Power Resistor, Wire Wound, 4 W, 5 %, ±200 ppm/°C, Axial-Leaded, Copper Termination, 20 x 7 x 8 mm, Loose Piece - Box, CGS SBC





TE Part # 1623728-3
BCHE 11 W 10R 5%



TE Part # CAT-C339-SB19B
Wirewound Resistor: Vertical Mount

Also in the Series | CGS SBC



Surface Mount Resistors(1)



Through-Hole Resistors(212)

Customers Also Bought



TE Part #1623773-7
C10 100R 5% (LOOSE)




TE Part #CAT-C339-SB19B
Wirewound Resistor: Vertical Mount



TE Part #4-1623773-2
C10 10R 5% (LOOSE)



TE Part #1-1617754-7
FCA-410-1620M=M83536/16-020M



TE Part #2-215309-0
2X20P HV100 REC CON. TE, 8.5MM



TE Part #3-1623774-1
C14 3K3 5% (LOOSE)



TE Part #8-1676913-9
YR1 0.1% 33K2



TE Part #160539-2
110 FASTON,REC.,20-17 AWG,TPBR

TE Part #ZPF00000000015130
DM 9718-37 S-A272



Documents

Product Drawings

BCHE 4 W 100R 5%

English

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

High Power Resistor - Type SBC (Square Ceramic) Series - Tyco Electronics Passives

English