

Product datasheet

Specifications



10w Display module, Harmony P6,
WXGA, 16M colors, PCAP Multi
Touch (2 points) with optimized
noise filter

HMIDM6500WC

EAN Code: 3606481808431

Main

Range of product	Harmony P6
Product or component type	Touch panel screen

Complementary

Display size	10.1 inch
Aspect ratio	16:9
Display colour	16 million colours
Pixel resolution	1280 x 800
Inrush current	30 A
Device mounting	Panel mounting Direct mounting VESA
Cut-out dimensions	255 (+ 1/- 0) x 185 (+ 1/- 0) mm
Width	268.5 mm
Height	198.5 mm
Net weight	2.0 kg

Environment

Product certifications	RCM KC UKCA DNV (DC model without HDD/fan/ EtherCAT card/22" wide display with expansion slot) ATEX zone 22 dust (DC model, front USB cover must be locked with screw) ATEX zone 2 (DC model, front USB cover must be locked with screw) CULus Class 1 Division 2 (without DIO option) IECEx zone 2 (DC model, front USB cover must be locked with screw) IECEx zone 22 (DC model, front USB cover must be locked with screw)
Ambient air temperature for operation	0...60 °C
Pollution degree	2
Operating altitude	2000 m
Shock resistance	147 m/s ² conforming to IEC 61131-2 147 m/s ² 3 shocks in each direction X, Y and Z

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	37.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	15.0 cm
Package 1 Length	36.0 cm
Package 1 Weight	2.6 kg
Unit Type of Package 2	P12
Number of Units in Package 2	30
Package 2 Height	150.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	88.0 kg

Logistical informations

Country of origin	FR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	375
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
F-gas usage performance	Only air and vacuum used for insulation / breaking, no F-gas including SF6
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
SCIP Number	D7229b34-b75f-4e38-8912-76d4fe04e192

Use Again


Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions

10-inch Wide Standard Model

External Dimensions




- (1) : Front
- (2) : Left
- (3) : Bottom

Mounting and Clearance


Mounting

Panel Cut Dimensions



A		B		C	
mm	in.	mm	in.	mm	in.
255 (+1, -0)	10.04 (+0.04, -0)	185 (+1, -0)	7.28 (+0.04, -0)	1.6...5	0.06...0.2

Mounting Angle



When installing this product in a slanted position, the product face should not incline more than 30°.

Clearance

