



6999 - ELBOW BODY POLYMER MALE BSPP FDA NICKEL PLD EPDM S



maximum working pressure	16 bar 2 MPa 232 psi
working temperature	-10 to 130 °C 14 to 266 °F 263 to 403 °K
vacuum capability	755 mm Hg
body	BIO-BASED POLYMER
sub-base	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	EPDM
gripping ring	STAINLESS STEEL

[Convert to inch](#)
[Convert to oz](#)
[Reset Filters](#)

Part Nb	ØD (MM)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	L (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
6999 04 10	4	G1/8	4.5	13	8.5	22.5	19	.009
6999 04 19	4	M5x0,8	3.5	8	8.5	23	19	.005
6999 06 10	6	G1/8	4.5	13	10.5	26.5	22.5	.011
6999 06 13	6	G1/4	5.5	16	10.5	26.5	22.5	.016
6999 06 19	6	M5x0,8	3.5	10	10.5	26.5	22.5	.008
6999 08 10	8	G1/8	4.5	13	13.5	35	29.5	.018
6999 08 13	8	G1/4	5.5	16	13.5	33	29.5	.02
6999 08 17	8	G3/8	5.5	20	13.5	33	29.5	.028
6999 10 13	10	G1/4	5.5	16	16	40.5	34	.029
6999 10 17	10	G3/8	5.5	20	16	39	34	.037
6999 10 21	10	G1/2	7	24	16	39	34	.042
6999 12 17	12	G3/8	5.5	20	19	42	40	.04
6999 12 21	12	G1/2	7	24	19	42	40	.049