

Drill Driver LXT®

DDF458

18V • 91 Nm • 2 000 min⁻¹

Rugged drill driver for heavy-duty use

A powerful tool with two speed ranges for screwdriving and drilling for professional use. Max. torque of 91 / 58 Nm. An ideal choice for jobs that require high power and torque. Integrated LED light.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 400 / 0 - 2000 min ⁻¹
Max. fastening torque Hard/Soft	91 / 58 Nm
Max Torque	110 Nm
Torque setting	21
Max. Drilling Diameter in Wood	76 mm
Max. Drilling Diameter in Steel	13 mm
Driving Shank	1/2"-20UNF "
Drill Chuck Capacity	1,5 - 13 mm
Drilling Capacity Wood (Auger Bit)	76 mm
Drilling Capacity Wood (Self-feed bit)	92 mm
Vibration Level, Drilling into metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Drilling into metal	1,5 m/s ²
Sound Pressure Level (L _{pA})	73 dB(A)

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery level indicator
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.dk



Related products

Other

User manual

Parts drawing