


**Part Number :** 5016462400

**Product Description :** 2.00mm Pitch, iGrid Receptacle Crimp Housing, Dual Row, Positive Lock, 24 Circuits, Natural

**Series Number :** 501646

**Status :** Active

**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[5016462400\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[5016462400.dxf](#)

### Specifications

[5016460000-A00.pdf](#)

[5016460000-A01.pdf](#)

[5016469200-200.pdf](#)

[5016460000-PS-000.pdf](#)

[5016461000-PS-000.pdf](#)

[5016461001-PS-001.pdf](#)

[PS-501646-001-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                |
|--------------------|--------------------------------|
| GADSL/IMDS         | Not Relevant                   |
| China RoHS         | per SJ/T 11365-2006            |
| EU ELV             | Compliant per 2000/53/EC       |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |

|            |  |
|------------|--|
| REACH SVHC | Not Contained per D(2025)4165-DC<br>(25 June 2025) |
| EU RoHS    | Compliant per EU 2015/863                          |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

|              |   |
|--------------|---|
| Status       | Active  |
| Category     | Connector Housings  |
| Series       | 501646  |
| Description  | 2.00mm Pitch, iGrid Receptacle<br>Crimp Housing, Dual Row, Positive<br>Lock, 24 Circuits, Natural |
| Application  | Signal, Wire-to-Board   |
| Product Name | iGrid   |
| UPC          | 822350087209  |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Physical

|                    |    |
|--------------------|----|
| Circuits (maximum) | 24 |
|--------------------|----|

|                               |                |
|-------------------------------|----------------|
| Color - Resin                 | Natural        |
| Flammability                  | 94V-0          |
| Gender                        | Receptacle     |
| Glow-Wire Capable             | No             |
| Keying to Mating Part         | None           |
| Lock to Mating Part           | Yes            |
| Material - Resin              | Nylon          |
| Number of Rows                | 2              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 2.00mm         |
| Pitch - Termination Interface | 2.00mm         |
| Polarized to Mating Part      | Yes            |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +105°C |

## Mates With / Use With

### Mates with Part(s)

| Description                                       | Part Number                   |
|---|-------------------------------|
| iGrid Vertical, Dual Row, Through Hole Headers    | <u><a href="#">501645</a></u> |
| iGrid Vertical, Dual Row, Through Hole Headers    | <u><a href="#">503091</a></u> |
| iGrid Right-Angle, Dual Row, Through Hole Headers | <u><a href="#">501876</a></u> |
| iGrid Right-Angle, Dual Row, Through Hole Headers | <u><a href="#">208659</a></u> |

### Use with Part(s)

| Description                  | Part Number                   |
|------------------------------|-------------------------------|
| iGrid Female Crimp Terminals | <u><a href="#">501647</a></u> |
| iGrid Female Crimp Terminals | <u><a href="#">501648</a></u> |
| iGrid Female Crimp Terminals | <u><a href="#">503095</a></u> |

This document was generated on Aug 08, 2025