

# Specifications for BMP71 Label Printer Labels

|                                     |  |
|-------------------------------------|--|
| <b>Adhesive</b>                     | Permanent Acrylic  |
| <b>After Process</b>                | Yes, this material will work with this application   |
| <b>Application</b>                  | Rating & Nameplate Labels  |
| <b>Approval/Compliance</b>          | UL Recognised; CSA Accepted; Halogen Free (DIN VDE 0472/part 815)  |
| <b>Article No.</b>                  | 114953   |
| <b>Board Application</b>            | Through Hole - Top   |
| <b>Brady Material No.</b>           | <a href="#">B-428</a>  |
| <b>Material Type</b>                | Metallised Polyester   |
| <b>Brand</b>                        | MetaLabel™ Series  |
| <b>Colour</b>                       | Silver   |
| <b>Finish</b>                       | Matt   |
| <b>Description</b>                  | Labels for the BMP™71 Label Printer. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use. |
| <b>Max. Characters per Line</b>     | 50   |
| <b>Max. Lines of Text</b>           | 10   |
| <b>Max. Service Temp. °C</b>        | 120  |
| <b>Order Reference</b>              | M71-22-428   |
| <b>Printer Compatibility</b>        | BMP71  |
| <b>Ribbon Series</b>                | M71-R4300  |
| <b>Shape</b>                        | Rectangle  |
| <b>Size - Height (mm)</b>           | 76.20  |
| <b>Size - Width (mm)</b>            | 25.40  |
| <b>Surface Mount Technology SMT</b> | No, this material does not work with this application  |
| <b>Through Hole Technology</b>      | Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No  |
| <b>Total Qty per</b>                | 100 Label(s) / Box   |

|                              |   |
|------------------------------|---|
| <b>Pack</b>                  |   |
| <b>Vertical Repeat (mm)</b>  | 79.38   |
| <b>Industry</b>              | Facility & Safety Identification;General Industry;Manufacturing;Process |
| <b>Min. Service Temp. °C</b> | -40   |
| <b>QTY. per Row</b>          | 1   |
| <b>Thickness (mm)</b>        | 0.112   |