

RD74LVC04B

Hex Inverters

REJ03D0217-0100Z Rev.1.00 Apr.08.2004

Description

The RD74LVC04B has six inverters in a 14-pin package. Low voltage and high-speed operation is suitable at the battery drive product (note type personal computer) and low power consumption extends the life of a battery for long time operation.

Features

- $V_{CC} = 1.65 \text{ V to } 5.5 \text{ V}$
- All inputs V_{IH} (Max.) = 5.5 V (@V_{CC} = 0 V to 5.5 V)
- Typical V_{OL} ground bounce < 0.8 V (@ V_{CC} = 3.3 V, Ta = 25°C)
- Typical V_{OH} undershoot > 2.0 V (@ V_{CC} = 3.3 V, Ta = 25°C)
- High output current ± 4 mA (@V_{CC} = 1.65 V) ± 8 mA (@V_{CC} = 2.3 V) ± 12 mA (@V_{CC} = 2.7 V) ± 24 mA (@V_{CC} = 3.0 V to 5.5 V)
- Ordering Information


Part Name	Package Type	Package Code	Package Abbreviation	Taping Abbreviation (Quantity)
RD74LVC04BFPEL	SOP-14 pin (JEITA)	FP-14DAV	FP	EL (2,000 pcs/reel)
RD74LVC04BTELL	TSSOP-14 pin	TTP-14DV	Т	ELL (2,000 pcs/reel)

Function Table

Input A	Output Y
Н	L
L	Н

H: High level L: Low level

Pin Arrangement



Absolute Maximum Ratings

Item	Symbol	Ratings	Unit	Conditions	
Supply voltage range	Vcc	-0.5 to 7.0	V		
Input diode current	l _{IK}	- 50	mA	$V_1 = -0.5 \text{ V}$	
Input voltage	Vı	-0.5 to 7.0	V	_	
Output diode current	Іок	- 50	mA	$V_0 = -0.5 \text{ V}$	
		50	mA	$V_O = V_{CC} + 0.5 V$	
Output voltage	Vo	-0.5 to V _{CC} +0.5	V	_	
Output current	lo	±50	mA	_	
V _{CC} , GND current / pin	I _{CC} or I _{GND}	100	mA		
Storage temperature	Tstg	-65 to +150	°C		

Note: The absolute maximum ratings are values, which must not individually be exceeded, and furthermore, no two of which may be realized at the same time.

Recommended Operating Conditions

Item	Symbol	Ratings	Unit	Conditions
Supply voltage	V _{CC}	1.5 to 5.5	V	Data hold
		1.65 to 5.5		At operation
Input / Output voltage	Vı	0 to 5.5	V	A
	Vo	0 to V _{CC}		Y
Operating temperature	Та	-40 to 85	°C	
Output current	I _{OH}	-4	mA	V _{CC} = 1.65 V
		- 8		$V_{CC} = 2.3 \text{ V}$
		- 12		$V_{CC} = 2.7 \text{ V}$
		-24		$V_{CC} = 3.0 \text{ V to } 5.5 \text{ V}$
	I _{OL}	4	mA	V _{CC} = 1.65 V
		8		$V_{CC} = 2.3 \text{ V}$
		12		$V_{CC} = 2.7 \text{ V}$
		24		$V_{CC} = 3.0 \text{ V to } 5.5 \text{ V}$
Input rise / fall time*1	t _r , t _f	20	ns/V	V _{CC} = 1.65 V to 2.7 V
		10		$V_{CC} = 3.0 \text{ V to } 5.5 \text{ V}$

Notes: 1. This item guarantees maximum limit when one input switches.

Waveform: Refer to test circuit of switching characteristics.

Electrical Characteristics

			Ta = -	-40 to 85°C		
Item	Symbol	V _{CC} (V)	Min	Max	Unit	Test Conditions
Input voltage	V _{IH}	1.65 to 1.95	V _{CC} ×0.65	_	V	
		2.3 to 2.7	1.7	_		
		2.7 to 3.6	2.0	_		
		4.5 to 5.5	V _{CC} ×0.7	_		
	V _{IL}	1.65 to 1.95	_	V _{CC} ×0.35	V	_
		2.3 to 2.7	_	0.7		
		2.7 to 3.6	_	0.8		
		4.5 to 5.5	_	V _{CC} ×0.3		
Output voltage	V _{OH}	1.65 to 5.5	V _{CC} -0.2	_	V	I _{OH} = -100 μA
		1.65	1.2	_		$I_{OH} = -4 \text{ mA}$
		2.3	1.7	_		$I_{OH} = -8 \text{ mA}$
		2.7	2.2	_		$I_{OH} = -12 \text{ mA}$
		3.0	2.4	_		
		3.0	2.2	_		$I_{OH} = -24 \text{ mA}$
		4.5	3.8	_		
	V_{OL}	1.65 to 5.5	_	0.2	V	I _{OL} = 100 μA
		1.65	_	0.45		I _{OL} = 4 mA
		2.3	_	0.7		$I_{OL} = 8 \text{ mA}$
		2.7	_	0.4		I _{OL} = 12 mA
		3.0	_	0.55		I _{OL} = 24 mA
		4.5	_	0.55		
Input current	I _{IN}	0 to 5.5	_	±5.0	μΑ	$V_{IN} = 5.5 \text{ V or GND}$
Quiescent supply	Icc	2.7 to 3.6	_	±5.0	μΑ	$V_{IN} = 3.6 \text{ V to } 5.5 \text{ V}$
current		2.7 to 5.5	_	5.0		$V_{IN} = V_{CC}$ or GND
	ΔI_{CC}	2.7 to 3.6	_	500	μA	V_{IN} = one input at $(V_{CC}$ -0.6)V, other inputs at V_{CC} or GND

Switching Characteristics

			Ta = -40 to 85°C				From	То
Item	Symbol	V _{CC} (V)	Min	Тур	Max	Unit	(Input)	(Output)
Propagation delay time	t _{PLH}	1.8±0.15	1.0	_	8.0	ns	Α	Υ
	t_{PHL}	2.5±0.2	1.0	_	7.5			
		2.7	1.0	_	5.5			
		3.3±0.3	1.0	_	4.5			
		5.0±0.5	1.0	_	4.0			
Between output pins skew*1	t _{OSLH}	1.8±0.15	_	_	_	ns		
	t_{OSHL}	2.5±0.2	_	_	_			
		2.7	_	_	_			
		3.3±0.3	_	_	1.0			
		5.0±0.5	_	_	1.0			
Input capacitance	C _{IN}	3.3	_	5.0	_	pF		

Note: 1. This parameter is characterized but not tested.


 $t_{\text{OSLH}} = | \; t_{\text{PLHm}} - t_{\text{PLHn}} |, \; t_{\text{OSHL}} = | \; t_{\text{PHLm}} - t_{\text{PHLn}} |$

Operating Characteristics


Та	=	25°	С

Item	Symbol	V _{cc} (V)	Min	Тур	Max	Unit	Test conditions
Power dissipation	C_PD	1.8	_	15	_	pF	f = 10 MHz
Capacitance		2.5	_	16	_		
		3.3	_	18	_		
		5.0	_	22	_		


Test Circuit




Waveforms



Package Dimensions





Renesas Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.

Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.

2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.

The information described here may contain technical inaccuracies or typographical errors.

Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.

Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (http://www.renesas.com).

4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.

5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system tha

- use.
 6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
 7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.

 Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.

 8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.



RENESAS SALES OFFICES

http://www.renesas.com

Renesas Technology America, Inc. 450 Holger Way, San Jose, CA 95134-1368, U.S.A Tel: <1> (408) 382-7500 Fax: <1> (408) 382-7501

Renesas Technology Europe Limited.

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, United Kingdom Tel: <44> (1628) 585 100, Fax: <44> (1628) 585 900

Renesas Technology Europe GmbHDornacher Str. 3, D-85622 Feldkirchen, Germany
Tel: <49> (89) 380 70 0, Fax: <49> (89) 929 30 11

Renesas Technology Hong Kong Ltd. 7/F., North Tower, World Finance Centre, Harbour City, Canton Road, Hong Kong Tel: <852> 2265-6688, Fax: <852> 2375-6836

Renesas Technology Taiwan Co., Ltd. FL 10, #99, Fu-Hsing N. Rd., Taipei, Taiwan Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology (Shanghai) Co., Ltd. 26/F., Ruijin Building, No.205 Maoming Road (S), Shanghai 200020, China Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

Renesas Technology Singapore Pte. Ltd.
1, Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632 Tel: <65> 6213-0200, Fax: <65> 6278-8001