

Product data sheet

Specifications



Repacked, modular surge arrester, Acti9, 1P+N, 350VAC, with remote transfer

A9L40501W



This repacked option saves 2.175 over the standard condition

Main

Range of product	IPRD
range of product	Acti9
Product name	Acti9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	iPRD40r
Device application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product certifications	CE
Quality labels	NF KEMA-KEUR
Poles description	1P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TT TN-S

Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV + GDT
[Ue] rated operational voltage	230 V AC (+/- 10 %) at 50/60 Hz
Nominal discharge current	Common mode: 15 kA (L/PE) Common mode: 15 kA (N/PE) Differential mode: 15 kA (L/N)
Maximum discharge current	Common mode: 40 kA L/PE Common mode: 40 kA N/PE Differential mode: 40 kA L/N
[Uc] maximum continuous operating voltage	Common mode: 260 V N/PE Differential mode: 350 V L/N
Maximum [Up] voltage protection level	Common mode <1.4 kV type 2 N/PE Differential mode <1.6 kV type 2 L/N
[Ut] temporary overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode 442 V L/PE 5 s withstand 1455 V L/PE 200 ms safe failure mode

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Disconnecter device type	Associated circuit breaker iC60H 40 A curve C - Icu 15 kA Associated circuit breaker IC60N 40 A curve C - Icu 10 kA Associated circuit breaker NG125H 40 A curve C - Icu 36 kA Associated circuit breaker NG125L 40 A curve C - Icu 50 kA Associated circuit breaker NG125N 40 A curve C - Icu 25 kA Associated fuse gG 63 A - Icu 15 kA Associated fuse gG 80 A - Icu 50 kA
Signalling circuit voltage	0.25 A/250 V AC 50/60 Hz
Mounting mode	Clip-on (DIN rail)
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	69 mm
Product weight	220 g
Colour	White (RAL 9003)
[Ipe] Ground residual current	0.003 mA 0.6 mA
Connections - terminals	Tunnel type terminal (top or bottom) 4...16 mm² flexible Tunnel type terminal (top or bottom) 4...16 mm² flexible with ferrule Tunnel type terminal (top or bottom) 2.5...25 mm² rigid
Wire stripping length	14 mm
Tightening torque	3.5 N.m
Compatibility code	IPRD40r

Environment

IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C
Circular nature	Repacked

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	9.800 cm
Package 1 Length	10.800 cm
Package 1 Weight	266.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	6
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.781 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

2 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

A9614fa2-07f8-47d1-a2fe-e27b32003d8d

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins