



Main

Range	OptiLine
Product name	OptiLine 45
Shape	Oval
Cabling installation system	Pole
Product type	Pole
Device presentation	Empty
Type of pole	One-sided
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted
Adjustment	Adjustable in height: 400 mm

Complementary

Additional information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front opening size	45 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	2700...3100 mm
Depth	89 mm
Width	68 mm
Cover type	1 closed cover cover 45 mm in aluminium anodized
Useful cross section	442 mm ²
Compartment partitioning	1 compartment

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating temperature	-25...60 °C
IP degree of protection	IP30

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations