


Features

- 94mm cubic-design LED multi-strobe beacon
- 4 different strobe patterns, can be switched externally
- High power LEDs, up to 64cd luminous intensity
- Good frontal and lateral signalling effect
- High degree of protection IP66
- Optional mounting type using metal bracket
- 24-48V AC/DC supply voltage

RS PRO Beacons

Auer Signal 0694321



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- 94mm cubic-design LED multi-strobe beacon
- 4 different strobe patterns, steady beacon, and flashing beacon, 3 can be switched externally.
- Modern LED technology with a service life source of >50,000 hours
- Ideal frontal and lateral signalling effect
- Can be mounted directly on walls horizontally or vertically.
- Offers a high degree of protection (IP66) and, with IK09, is particularly used in extreme conditions.
- Combinations of beacons and multi-tone alarm sounders possible
- For industrial, plant construction, logistics and general applications
- Full mounting accessory package available

General Specifications

Lens	Polycarbonate
Bulb Type	LED
Light Effect	Double strobe 1.4Hz. 6x strobe 1.0Hz. Multi-strobe
Lens Colour	Red. Polycarbonate, ribbed inside
Type of mounting	Any
Fitting	4 bolt
Flash Pattern	Multi strobe beacon
Housing Colour	Red
Lamp Include	Yes
Multifunction	Yes
Number of LED	4 high power LEDs
Protection	Against water & dust, vibration (IK09)

Electrical Specifications

Supply Voltage	24-48V AC/DC
Light Output	64 Cd
Current Type	AC/DC
Current Consumption	300mA

Mechanical Specifications

Dimensions	94mm (w) x 99mm (d) x 94mm (h)
Base Diameter	94mm
Base Length	99mm
Base Width	94mm
Mounting Style	Screw Mount
Weight	300g

Operation Environment Specifications

Maximum Temperature	+60°C
Minimum Temperature	-30°C

Protection Category

IP Rating	IP66
------------------	------

Approvals

Compliance/Certifications	CE / UL
Declarations	RoHS Compliant / REACH
Standards Met	Yes
Hazardous Area Certification	N/A

