

Hedge Trimmer LXT®

DUH601

18V • 600 mm

Model DUH601 is a brushless hedge trimmer powered by an 18V Li-ion battery.

A cordless hedge trimmer with a brushless motor and 600 mm blade for gardening. Features a double sided curved blade. Both sides with triple edged cutting teeth. Two-handed safety switches offer added safety and the tool has low noise levels. Three speed settings to suit different applications. Excellent for professional use. One 5.0 Ah batterie and a rapid charger.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Strokes per Minute (SPM)	2000 / 3600 / 4400 min ⁻¹
Length Of Blade	600 mm
Max blade opening	23,5 mm
Tooth Spacing	35 mm
Sound Power Level (L _{WA})	91 dB(A)
Sound Pressure Level (L _{pA})	83 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	≤ 2,5 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²
Product Dimensions (L x W x H):	1121 x 225 x 192 mm

User benefits

- Brushless maintenance-free and long-life motor
- Soft start for smooth start-ups
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Variable speed
- Electric brake for maximum productivity and increased operator safety
- Double action switch for increased safety
- Constant speed control maintains constant speed under load
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Optimum blade shape for smooth cutting and long run time

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing