

PRODUCT CODE		2760C-M	MINI COMPACT LEVER ARM RIVETER			
DIMENSIONAL CRITERIA		SPECIFICATION	Supplier Inspections			
1						
2						
3	Nose dia. length and A/f size	23.5 dia. x 31mm long & 24mm a/f				
4	Body	Plastic moulding on steel				
5	Body width, breadth and length	60 x 47 x 63.4mm excl. nut				
6	Levers	Steel formed to 25 x 14 x 2mm thick. Black painted				
7	Lever length from Body	200 ± 5mm				
8	Levers to Body	Spring loaded and secured by M6 Cap screws & lock nuts				
9	Grip	Blue Plastic				
10	Grip section at Mid-point	27 x 25mm ± 1mm				
11	Grip Length	122 ± 5mm				
12						
13	Grip span closed	130 ± 5mm				
14						
15	Nose inserts x 5 (colour banded)	2.4, 3.2, 4.0, 4.8 & 6.4mm				
16						
17	Product no. moulded into Body back	2760C-M				
18	Overall length with Nose insert fitted	260 ± 5mm				
19	Weight	0.766 ± 0.03kg				
20						
21	Barcode on back of Printed Card	5012095617839				
22						
23	Packed	5 per carton				
24						
25						
26						
27						



Blue Grips