




Connectors > Pluggable IO Connectors & Cages > zSFP+ Stacked Cage Assembly: Gasket



Form Factor: **zSFP+ Stacked (SFP28)**

Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**

Centerline (Pitch): **.8 mm [.032 in]**

Sealable: **No**

Circuit Application: **Signal**

[All zSFP+ Stacked Cage Assembly: Gasket \(34\)](#)

Features

Product Type Features

Cage Type	Stacked
Form Factor	zSFP+ Stacked (SFP28)
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Sealable	No

Configuration Features

Lightpipe Style	Standard
Number of Positions	40
Number of Ports	2
Port Matrix Configuration	2 x 1

Electrical Characteristics

Data Rate (Max)	32 Gb/s
-----------------	---------

Contact Features

Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
--------------------------------------	--



Tail Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 μm[29.92 μin]

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	1.8 mm[.07 in]

Housing Features

Cage Material	Nickel Silver Alloy
Centerline (Pitch)	.8 mm[.032 in]

Dimensions

PCB Thickness (Recommended)	1.5 mm[.059 in]
-----------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Pluggable I/O Applications	zSFP+ Thermally Enhanced
Heat Sink Compatible	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tray
------------------	------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Elastomeric Gasket

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241)



Does not contain REACH SVHC


Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2334985-2 SFP28 DIRECT ATTACH CA, 1M, 32AWG	 TE Part # 4-2821224-5 SFP56 DIRECT ATTACH CA, 3M, 26AWG	 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N49011 SFP28 to SFP28 Cable Assembly: 26 AWG
 TE Part # CAT-C11-N490111 SFP28 to SFP28 Cable Assembly: 28 AWG	 TE Part # CAT-C11-N4901114 SFP28 to SFP28 Cable Assembly: 30 AWG	 TE Part # 4-2821222-5 SFP56 DIRECT ATTACH CA, 2M, 30AWG	 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG
 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG	 TE Part # 2215000-1 Kit, seating tool, zSFP+, 2X1	 TE Part # 4-2334985-2 SFP56 DIRECT ATTACH CA, 1M, 32AWG


Customers Also Bought



TE Part #2170088-1
ZSFP+ Connector,30u"



TE Part #1-2324271-2
LEFT SEGMENT LGA4189-4 SOCKET-
P4 FOR ODM



TE Part #2-2330553-1
SOCKET P4/P5 DUST COVER,
LGA4189



TE Part #2344604-1
50 AMP CARD EDGE ASSEMBLY




TE Part #2227728-1
zSFP+ 1x2 Cage Assy, Press-Fit




TE Part #2-2330550-1
SOCKET P4 BOLSTER PLATE ASSY, W
/O COVER




TE Part #2013499-1
MICRO USB, TYPE B



TE Part #2-2129710-1
LEFT SIDE LGA3647-0 SOCKET-P0
FOR ODM



TE Part #2368060-5
DDR4 DIMM 288 PIN SMT TYPE



TE Part #2368060-6
DDR4 DIMM 288 PIN SMT TYPE

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2198318-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2198318-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2198318-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

zSFP+ Interconnect Brochure

English

Product Specifications



Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English