

Garant CEE 2 IP 44 industrial/construction cable reel 25 m H07RN-F 3G2.5

For construction site use according to DGV 203-006 (formerly BGI 608) and for permanent outdoor use, IP 44.



MADE IN GERMANY



Product number 1182760300
EAN 4007123702800

DESCRIPTION

- Reel body made of special plastic on a galvanized support frame.
- Innovative “cablepilot” carrying handle for perfect cable guidance. Swivels on both sides and allows comfortable carrying and hanging.
- With rotating handle for convenient winding.
- RN cable approved for demanding construction conditions according to VDE 0100 Part 704.
- CEE plug 230 V/16 A.
- 2 CEE sockets 230 V/16 A.
- With single-pole safety cut-out and overheating protection.
- Equipment category 2 (K2 DGV 203-005): suitable for harsh operation with high mechanical, physical and chemical stress.

TECHNICAL DATA

Cable quality	Rubber-Neoprene
Cable length	25 m
Cable designation	H07RN-F 3G2,5
Cable colour	black
Reel diameter	290 mm
Plug system CEE socket	CEE 2x 16 A 2P+E (3p) 230 V

Plug system socket	Without
Plug system plug	CEE 16 A 2P+E (3p) 230 V
Max. current carrying capacity	16 A
Nominal input voltage	230 V
Degree of protection (IP)	IP44

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	6.65 kg
Dimension LxWxH (without packing)	22 cm x 29 cm x 37 cm

Weight of product (including packaging)	6.66 kg
Dimension LxWxH (incl. packing)	22 cm x 29 cm x 37 cm

SCOPE OF DELIVERY

Garant CEE 2 IP44 industrial/construction cable reel
Hugo Brennenstuhl GmbH & Co. KG

www.brennenstuhl.com

All products are subject to technical changes.